

SonicLine® Specification

Please complete this form and return it to your nearest GEMÜ office or to the address listed below!

Date: _____

Application: _____

Medium: _____

Concentration: _____

Viscosity: _____

Pressure / psi: min.: max.:

Flow l/min: min.: max.:

Kv (m³/h) Kv:

Operating temperature:

Fluid / °C: min.: max.:

Ambient / °C: min.: max.:

Size / range: 3/8" / 0.03 - 6 l/min
 3/8" / 0.09 - 6 l/min
 1/2" / 0.3 - 24 l/min
 3/4" / 0.9 - 60 l/min
 1" / 1.2 - 120 l/min

Output:

Digital 1: pulse* *Factory setting
dosing
empty tube alarm

Digital 2: empty tube alarm*
dosing

Analog: 4-20mA* / 2-10V
0-20mA / 0-10V

Quantity:

System in use: _____

The technical details of each enquiry will be checked by GEMÜ.

Contact (GEMÜ):	_____
Customer:	_____
Department:	_____
Address:	_____
Phone:	_____
Fax:	_____
e-mail:	_____