



GEMÜ 539 eSyDrive



GEMÜ 549 eSyDrive



GEMÜ 649 eSyDrive

GEMÜ eSyDrive Motorized linear actuator

Areas of application

- Pharmaceutical, biotechnology and cosmetics industries
- Foodstuffs and beverages
- Chemical engineering
- Power generation and environmental engineering
- Mechanical engineering and processing industry

Features

- Open/close function, position and process control
- Available as diaphragm valve, angle seat globe valve and globe valve
- 3 actuator sizes available
- Variable force and speed
- Diagnostic functions
- Hygienic design
- Self-locking
- Energy-efficient

Description

Designed on the basis of the hollow shaft principle in conjunction with technology that does not use brushes or sensors, the GEMÜ eSyDrive actuator sets new standards in terms of service life, compactness, actuating speed and energy efficiency. The self-locking actuator also offers a high level of reproducibility for positioning and is therefore particularly suitable for use in precise control applications. The Ethernet-based eSy-web interface, in conjunction with an integrated web server, enables the exchange of parametrization and diagnostics data and the networking of several devices.

Technical specifications

- Nominal sizes*:
DN 10 to 100
- Ambient temperature:
-10 to 60 °C
- Protection class
IP65
- Actuating speed*:
Max. 4 to 6 mm/s
- Energy supply:
24 V DC

*depending on version and/or operating parameters

Applications

- Variable, complex open/close and control applications
- Applications with stringent requirements regarding performance and service life
- Energy-efficient alternatives to pneumatic globe and diaphragm valves
- Applications with contamination risks due to compressed air
- Compact systems without separate compressed air supply
- Mobile systems

Communicative
eSy-Web interface
(Ethernet, browser-based), Modbus TCP

Easy to operate
On-site operation

Safe
Standard manual override, external emergency power supply module (optional)

Visible
Electrical high visibility status and position indicator, mechanical position indicator

Precise
Force and speed parametrization

Variable
Linear actuator for globe and diaphragm valves

