

GEMÜ C67 CleanStar

Manually operated diaphragm valve



Features

- High purity due to cleanroom manufacturing
- High Flow version selectable
- High flow rate with low-stress media channelling
- Minimal deadleg
- Optional flow direction
- Also available as T valve
- The valve is available with an ECTFE union nut as an option.
- Reduced costs thanks to long service life

Description

The GEMÜ C67 HPW CleanStar ultra pure 2/2-way diaphragm valve is manually operated. All media wetted parts are made of PFA or PTFE. A seal adjuster (not with actuator size 4) and optical position indicator are integrated as standard. This High Purity version of the CleanStar series complies with the strictest purity standards and boasts high chemical resistance. It can also be used with high media temperatures. As such, it is often used at the supply and distribution level in semiconductor factories.

Technical specifications

- **Media temperature :** -10 to 150 °C
 - **Ambient temperature:** 0 to 60 °C
 - **Operating pressure :** 0 to 6 bar
 - **Nominal sizes:** DN 4 to 50
 - **Body configurations:** 2/2-way body | T-body | V valve body
 - **Connection types:** Flare | Flare SpaceSaver | Nexus Connect® SpaceSaver | PrimeLock® | PrimeLock® SpaceSaver | Spigot | Super 300 Type Pillar® SpaceSaver | Union end | Welded-on Nexus Connect®
 - **Connection standards:** DIN
 - **Body materials:** PFA | PP-H, natural | PP-R, natural | PVDF
 - **Diaphragm materials:** PTFE/EPDM
 - **Conformities:** EAC | FDA | TA Luft (German Clean Air Act)
- Technical data depends on the respective configuration



further information
webcode: GW-C67



Contents

| | |
|--|-----------|
| 1 CleanStar product line..... | 4 |
| 2 Product description..... | 5 |
| 3 Designs..... | 6 |
| GEMÜ C67 CleanStar PFA | 8 |
| 4 Availability C67 PFA..... | 9 |
| 4.1 Body configuration - 2/2-way body (code D) | 9 |
| 4.1.1 Materials | 9 |
| 4.2 Connections..... | 10 |
| 4.2.1 Body configuration - 2/2-way body (code D)..... | 10 |
| 4.2.2 Body configuration - T body (code T)..... | 13 |
| 5 Order data C67 PFA | 14 |
| 5.1 Order data - body configuration - 2/2-way body (code D)..... | 14 |
| 5.2 Order data - body configuration - T body (code T) | 16 |
| 6 Technical data C67 PFA | 18 |
| 6.1 Medium | 18 |
| 6.2 Temperature | 18 |
| 6.3 Pressure | 18 |
| 6.4 Product conformities | 21 |
| 6.5 Mechanical data | 21 |
| 7 Dimensions C67 PFA..... | 22 |
| 7.1 2/2-way valves (code D)..... | 22 |
| 7.1.5 Nexus Connect® (code NX) | 27 |
| 7.2 T body (code T) | 28 |
| 7.3 Mounting dimensions | 31 |
| GEMÜ C67 CleanStar PFA 3/5-way | 32 |
| 8 Availability C67 PFA 3/5-way | 33 |
| 8.1 Connections..... | 33 |
| 8.2 Actuator assignments..... | 33 |
| 9 Order data C67 PFA 3/5-way | 34 |
| 9.1 Order codes | 34 |
| 9.2 Order example | 35 |
| 10 Technical data C67 PFA 3/5-way..... | 36 |
| 10.1 Medium | 36 |
| 10.2 Temperature | 36 |
| 10.3 Pressure | 36 |
| 10.4 Product conformities | 38 |
| 10.5 Mechanical data | 38 |
| 11 Dimensions C67 PFA 3/5-way | 38 |
| GEMÜ C67 CleanStar PVDF | 39 |
| 12 Availability C67 PVDF | 40 |

| | |
|---|-----------|
| 13 Order data C67 PVDF | 41 |
| 13.1 Order codes | 41 |
| 13.2 Order example | 41 |
| 14 Technical data C67 PVDF..... | 42 |
| 14.1 Medium | 42 |
| 14.2 Temperature | 42 |
| 14.3 Pressure | 42 |
| 14.4 Product conformities | 42 |
| 14.5 Mechanical data | 42 |
| 15 Dimensions C67 PVDF | 43 |
| 15.1 Union end (code 7, 78) | 43 |
| 15.2 Connection dimensions | 43 |
| 15.3 Mounting dimensions | 44 |
| GEMÜ C67 CleanStar SmartLine | 45 |
| 16 Availability C67 SmartLine | 46 |
| 17 Order data C67 SmartLine | 47 |
| 17.1 Order codes | 47 |
| 17.2 Order example | 47 |
| 18 Technical data C67 SmartLine..... | 48 |
| 18.1 Medium | 48 |
| 18.2 Temperature | 48 |
| 18.3 Pressure | 48 |
| 18.4 Product conformities | 49 |
| 18.5 Mechanical data | 49 |
| 19 Dimensions C67 SmartLine | 49 |
| 19.1 Flare connection (code 75, 77) | 49 |
| 19.2 Butt weld spigot (code 20)..... | 50 |
| 19.3 Union end (code 78) | 51 |
| 19.4 Mounting dimensions | 52 |
| 20 Accessories | 53 |
| GEMÜ CFSTF | 53 |
| GEMÜ 1098 | 53 |
| GEMÜ FlareStar | 53 |
| GEMÜ TubeStar | 53 |
| GEMÜ C67 STA | 53 |

CleanStar product line

| |  |  |  |  |
|--------------------------------------|---|---|--|---|
| GEMÜ C67 Clean- Star PFA | ● | ● | ● | ● |
| GEMÜ C67 Clean- Star PFA 3/5-way | | ● | | |
| GEMÜ C67 Clean- Star PVDF | | | ● | |
| GEMÜ C67 Clean- Star SmartLine | | | | ● |
| Operation | | | | |
| Manual | ● | ● | ● | ● |
| Nominal sizes | DN 4 to 50 | DN 10 to 15 | DN 15 | DN 10 to 32 |
| Media temperature | -10 to 150 °C | -10 to 150 °C | -10 to 120 °C | -10 to 80 °C |
| Connection types | | | | |
| Butt weld spigot | ● | - | - | ● |
| Flare | ● | ● | - | ● |
| Flare SpaceSaver | ● | ● | - | - |
| Nexus Connect® SpaceSaver | ● | - | - | - |
| PrimeLock® | ● | - | - | - |
| PrimeLock® SpaceSaver | ● | - | - | - |
| Super 300 Type Pillar® SpaceSaver | ● | - | - | - |
| Tube spigot | ● | - | - | - |
| Union end | - | - | ● | ● |
| Welded-on Nexus Con- nect® | ● | - | - | - |
| Body materials | | | | |
| PFA | ● | ● | - | - |
| PP-H | - | - | - | ● |
| PP-R | - | - | - | ● |
| PVDF | - | - | ● | - |
| Body configuration | | | | |
| 2/2-way body | ● | - | ● | ● |
| T-body | ● | - | - | - |
| V valve body | - | ● | - | - |
| Conformities | | | | |
| EAC | ● | ● | ● | ● |
| FDA | ● | ● | ● | ● |
| TA Luft (German Clean Air Act) | ● | ● | ● | ● |




Product description






| No. | Name | Materials |
|-----|-----------------------|----------------------------|
| 1 | Seal adjuster | |
| 2 | Actuator | PVDF (body) |
| 3 | Position indicator | |
| 4 | Actuator union nut | PVDF or ECTFE |
| 5 | Union nut connections | PVDF, PFA or CPFA |
| 6 | Mounting lugs | |
| 7 | Valve body | PVDF or PFA |
| | Diaphragm (internal) | PTFE (media wetted) / EPDM |

Designs

Body configurations

| Body configuration | Description |
|--|---|
| 2/2-way body (code D)  | The 2/2-way body is the most commonly used body configuration. Thanks to the seal created by the weir-style body, the flow direction is freely selectable. Various pipe and tube connections can be connected to the ports, whereby both connections (X and Z) have the same connection size. However, different connection sizes can also be used by attaching corresponding fittings. |
| T valve body (code T)  | The T body has 3 connections. The opposing connections (X and Z) are classed as main pipe, as media flows between them at all times, regardless of the position (open/closed) of the actuator. The branch (Y) is located at a 90° angle to the main pipe. The flow across this connection can be influenced via the actuator. T valves are often used when regular analyses of the medium are required. To this end, the branch (Y) is opened briefly to remove a small volume of the medium as and when necessary. T valves are often also installed in a ring main, whereby the medium from the ring main is only released via the Y connection when the actuator is in its open position. |
| V valve (code V)  | The V valve body has 3 connections, two of which (X and Z) can be controlled via valve seats. The following flow schemes can therefore be implemented: <ul style="list-style-type: none"> • Flow between X and Y, as well as between Z and Y (both actuators open) • No flow (both actuators closed) • Flow only between X and Y (one actuator open, one actuator closed) • Flow only between Z and Y (one actuator open, one actuator closed) This diaphragm valve can be configured with two pneumatic and two manual actuators. A combination of both actuator types is also possible. V valves are often used when media need to be mixed at a specific mixing ratio. However, they can also be used to establish redundant media supply or as a mixing valve. |

Special versions

| | Description |
|---|--|
| High Flow (code F)   | <p>In actuator sizes 2 and 3, the 2/2-way body is also available in a so-called High Flow design. This body version has a flow-optimized weir geometry. This reduces the pressure loss and thereby facilitates a higher flow. High Flow valve bodies are often used when higher volume flows are required.</p> <p>The upper image shows a cross-section of a standard version without High Flow. The lower image shows a cross-section of a High Flow design (code F).</p> |
| ECTFE union nut (code E)  | <p>The central union nut, which connects the actuator to the body via a thread, can optionally be ordered in ECTFE. This design is used if the outside environment where the valve is used contains alkaline media. In conditions such as these, a central union nut made from ECTFE can offer improved mechanical and chemical resistance. The materials can be distinguished based on their colour. In comparison with the white PVDF material, ECTFE has a slightly darker colour. The material is also uniquely indicated via an arrow on the union nut.</p> |

GEMÜ C67 CleanStar PFA

Manually operated diaphragm valve with PFA valve body



Features

- High purity due to cleanroom manufacturing
- High Flow version selectable
- High flow rate with low-stress media channelling
- Minimal deadleg
- Optional flow direction
- Also available as T valve
- The valve is available with an ECTFE union nut as an option.
- Reduced costs thanks to long service life

Description

The GEMÜ C67 HPW CleanStar ultra pure 2/2-way diaphragm valve is manually operated. All media wetted parts are made of PFA or PTFE. A seal adjuster (not with actuator size 4) and optical position indicator are integrated as standard. This High Purity version of the CleanStar series complies with the strictest purity standards and boasts high chemical resistance. It can also be used with high media temperatures. As such, it is often used at the supply and distribution level in semiconductor factories.

Technical specifications

- **Media temperature :** -10 to 150 °C
- **Ambient temperature:** 0 to 60 °C
- **Operating pressure :** 0 to 6 bar
- **Nominal sizes:** DN 4 to 50
- **Body configurations:** 2/2-way body | T-body
- **Connection types:** Butt weld spigot | Flare | Flare SpaceSaver | Nexus Connect® SpaceSaver | PrimeLock® | PrimeLock® SpaceSaver | Super 300 Type Pillar® SpaceSaver | Tube spigot | Welded-on Nexus Connect®
- **Connection standards:** DIN
- **Body materials:** PFA
- **Diaphragm materials:** PTFE/EPDM
- **Conformities:** EAC | FDA | TA Luft (German Clean Air Act)

Technical data depends on the respective configuration

Availability C67 PFA

Body configuration - 2/2-way body (code D)

Materials

| International code | DN | Connection size X, Z | Connection type (code) ¹⁾ | | | |
|------------------------|-----------|----------------------|--------------------------------------|-----------|---------------|--------------------|
| | | | 30 | NX welded | NX SpaceSaver | 73, 75, 77, PL, T3 |
| PFA material (code 30) | | | | | | |
| 4 | 4 | 1/4" tube | - | X | - | X |
| | 10 | 1/4" pipe | X | - | - | - |
| 6 | 6 | 3/8" tube | - | X | X | X |
| 8 | 10 | 1/2" tube | - | X | X | X |
| | 15 | 1/2" pipe | X | - | - | - |
| 12 | 15 | 3/4" tube | - | X | X | X |
| | 20 | 3/4" pipe | X | - | - | - |
| 16 | 20 | 1" tube | - | X | X | X |
| | 25 | 1" pipe | X | - | - | - |
| 20 | 25 | 1 1/4" tube | - | - | - | X |
| 24 | 40 | 1 1/2" pipe | X | - | - | - |
| 32 | 50 | 2" pipe | X | - | - | - |

1) **Connection type**

Code 30: Spigot – inch, for welding or solvent cementing, depending on the body material

Code 73: Flare connection with CPFA union nut

Code 75: Flare connection with PVDF union nut

Code 77: Flare connection with PFA union nut


Code NX: Nexus Connect connection with PFA union nut

Code PL: PrimeLock connection

Code T3: Tube spigot

Connections

Body configuration - 2/2-way body (code D)



Connection type Flare (code 73, 75, 77)

| Actuator size (code) | Connection size (code) | SpaceSaver position | | | |
|-------------------------|---------------------------|---------------------|-----------------------|-----------------------------------|--|
| | | None | On one side Pos. X | On one side Pos. Z (code Z) | On both sides Pos. X, Z (code S) |
| 1, 1E | 4 | X | On request | X | - |
| | 6 | X | On request | X | - |
| 2, 2E | 8 | X | On request | X | X |
| | 12 | X | On request | X | X |
| 3, 3E | 12 | X | On request | X | X |
| | 16 | X | On request | X | X |
| | 20 | X | On request | X | X |

Connection type Flare (code 73, 75, 77) – High Flow design

| Actuator size (code) | Connection size (code) | SpaceSaver position | | | |
|-------------------------|---------------------------|---------------------|-----------------------|-----------------------------------|--|
| | | None | On one side Pos. X | On one side Pos. Z (code Z) | On both sides Pos. X, Z (code S) |
| 2 F, 2EF | 12 | X | On request | - | - |
| 2 F, 2EF | 16 | X | On request | - | - |
| 3 F, 3EF | 16 | X | On request | - | - |
| 3 F, 3EF | 20 | X | On request | X | X |

Connection type butt weld spigot (code 30)

| Actuator size (code) | Connection size X, Z (code) | Butt weld spigot | |
|-------------------------|--------------------------------|------------------|---------------------|
| | | On both sides | On one side, pos. Z |
| 1, 1E | 4 | X | - |
| 2, 2E | 8 | X | X |
| 2, 2E | 12 | X | X |
| 3, 3E | 12 | X | X |
| 3, 3E | 16 | X | X |
| 4 | 24 | X | - |
| 4 | 32 | X | - |

Connection type butt weld spigot (code 30) - High Flow design

| Actuator size (code) | Connection size X, Z (code) | Butt weld spigot | |
|-------------------------|--------------------------------|------------------|---------------------|
| | | On both sides | On one side, pos. Z |
| 2 F | 8 | X | - |
| 2 F | 12 | X | - |
| 3 F | 16 | X | - |

Connection type Flare in pos. X, butt weld spigot in pos. Z (code K)

| Actuator size (code) | Actuator size (code) | Connection type (code) | |
|----------------------|----------------------|------------------------|---------------------|
| | | 73, 75, 77 | 30 |
| | | On one side, pos. X | On one side, pos. Z |
| 2, 2E | 8 | X | X |
| 2, 2E | 12 | X | X |
| 3, 3E | 12 | X | X |
| 3, 3E | 16 | X | X |

Connection type Flare in pos. X, butt weld spigot in pos. Z (code K) – High Flow design

| Actuator size (code) | Actuator size (code) | Connection type (code) | |
|----------------------|----------------------|------------------------|---------------------|
| | | 73, 75, 77 | 30 |
| | | On one side, pos. X | On one side, pos. Z |
| 2 F, 2EF | 12 | X | X |
| 2 F, 2EF | 16 | X | X |
| 3 F, 3EF | 16 | X | X |

PrimeLock® connection type (code PL)

| Actuator size (code) | Connection size (code) | Pos. SpaceSaver | |
|----------------------|------------------------|-----------------|--|
| | | Without | |
| 1, 1E | 4 | X | |
| | 6 | X | |
| 2, 2E | 8 | X | |

PrimeLock® (code PL) connection type – High Flow design

| Actuator size (code) | Connection size (code) | Pos. SpaceSaver | |
|----------------------|------------------------|-----------------|--|
| | | Without | |
| 2 F, 2EF | 12 | X | |
| | 16 | X | |
| 3 F, 3EF | 16 | X | |
| | 20 | X | |

Connection type tube spigot (code T3)

| Actuator size (code) | Connection size (code) | SpaceSaver position | |
|----------------------|------------------------|---------------------|--|
| | | None | |
| 1, 1E | 6 | X | |
| 2, 2E | 8 | X | |
| | 12 | X | |
| 3, 3E | 16 | X | |

Connection type tube spigot (code T3) – High Flow design

| Actuator size (code) | Connection size (code) | SpaceSaver position | |
|----------------------|------------------------|---------------------|--|
| | | None | |
| 3 F, 3EF | 20 | X | |


Nexus Connect® connection type (code NX) - Standard (1, 2, 3), High Flow design (2F, 3F)

| Actuator size (code) | Connection size | Connection | |
|----------------------|-----------------|---------------|------------|
| | | On both sides | |
| | | Welded | SpaceSaver |
| 1 | 1/4" | X | - |

Availability C67 PFA

| Actuator size (code) | Connection size | Connection | |
|-------------------------|-----------------|---------------|------------|
| | | On both sides | |
| | | Welded | SpaceSaver |
| 2 | 3/8" | X | X |
| | 1/2" | X | X |
| | 3/4" | X | - |
| 2F | 3/4" | - | X |
| 3 | 1" | X | - |
| 3F | 1" | - | X |

Body configuration - T body (code T)



Connection type Flare (code 73, 75, 77)

| Actuator size (code) | Connection size X, Z (code) | Connection size Y (code) | SpaceSaver position | | | | |
|-------------------------|-----------------------------------|--------------------------------|---------------------|---|---|---|---------------|
| | | | None | X | Y | Z | X, Z (code S) |
| 1, 1E | 6 | 4 | X | - | - | - | - |
| | 6 | 6 | X | - | - | - | - |
| | 8 | 6 | X | - | - | X | - |
| | 12 | 6 | X | X | - | X | - |
| 2, 2E | 8 | 8 | X | X | X | X | X |
| | 12 | 8 | X | X | X | X | X |
| | 12 | 12 | X | X | X | X | - |
| | 16 | 8 | X | X | - | X | X |
| | 16 | 12 | X | X | X | X | - |
| 3, 3E | 16 | 16 | X | X | - | X | - |
| | 20 | 8 | X | - | - | X | - |
| | 20 | 12 | X | - | - | X | - |
| | 20 | 16 | X | - | - | X | - |
| | 20 | 20 | X | - | - | X | - |

Connection type butt weld spigot (code 30)

| Actuator size (code) | Connection size X, Z (code) | Connection size Y (code) | Butt weld spigot, pos. X, Y, Z | Butt weld spigot, pos. X, Z | |
|-------------------------|-----------------------------------|-----------------------------|-----------------------------------|-----------------------------|-----------------------------|
| | | | | SpaceSaver, pos. Y | Flare connection, pos. Y |
| 1, 1E | 4 | 4 | X | - | - |
| | 8 | 4 | X | - | - |
| 2, 2E | 8 | 8 | X | X | - |
| | 12 | 8 | X | - | - |
| | 12 | 8 | X | - | X |
| | 12 | 12 | - | - | X |
| 3, 3E | 16 | 8 | X | X | X |
| | 16 | 12 | X | - | - |
| | 16 | 16 | X | X | X |

Order data C67 PFA

Order data - body configuration - 2/2-way body (code D)

Order codes

The order data provide an overview of standard configurations.

Please check the availability before ordering. Other configurations available on request.

| 1 Type | Code |
|--|------|
| Diaphragm valve, manually operated, plastic handwheel, seal adjuster | C67 |

| 2 Position of space saver | Code |
|--|------|
| Without | |
| Flare connection in position X, butt weld spigot in position Z | K |
| Space Saver for X+ Z position | S |
| Space Saver for Z position | Z |

| 3 Connection size | Code |
|--------------------------------|------|
| 1/4", international code: 4 | 4 |
| 3/8", international code: 6 | 6 |
| 1/2", international code: 8 | 8 |
| 3/4", international code: 12 | 12 |
| 1", international code: 16 | 16 |
| 1 1/4", international code: 20 | 20 |
| 1 1/2", international code: 24 | 24 |
| 2", international code: 32 | 32 |

| 4 Body configuration | Code |
|----------------------|------|
| 2/2-way body | D |

| 5 Connection type | Code |
|---|------|
| Tube | |
| Flare connection with CPFA union nut | 73 |
| Flare connection with PVDF union nut | 75 |
| Flare connection with PFA union nut | 77 |
| Nexus Connect connection with PFA union nut | NX |
| PrimeLock connection | PL |
| Tube spigot | T3 |
| Pipe | |
| Spigot – inch, for welding or solvent cementing, depending on the body material | 30 |

| 6 Valve body material | Code |
|-----------------------|------|
| PFA, perfluoroalkoxy | 30 |

| 7 Diaphragm material | Code |
|----------------------|------|
| PTFE/EPDM one-piece | 54 |
| PTFE/EPDM two-piece | 5M |

| 8 Control function | Code |
|--------------------|------|
| Manually operated | 0 |

| 9 Actuator version | Code |
|---|------|
| Standard version | |
| Actuator size 1 | 1 |
| Actuator size 2 | 2 |
| Actuator size 3 | 3 |
| Actuator size 4 | 4 |
| Standard version with ECTFE union nut | |
| Actuator size 1, with ECTFE union nut | 1E |
| Actuator size 2, with ECTFE union nut | 2E |
| Actuator size 3, with ECTFE union nut | 3E |
| High Flow design | |
| Actuator size 2 High Flow | 2 F |
| Actuator size 3 High Flow | 3 F |
| High Flow design with ECTFE union nut | |
| Actuator size 2 High Flow, with ECTFE union nut | 2EF |
| Actuator size 3 High Flow, with ECTFE union nut | 3EF |

| 10 Design | Code |
|---|------|
| Without | |
| CleanStar with welded-on NexusConnect fitting | 2591 |

| 11 High Purity version | Code |
|------------------------|------|
| High purity white | HPW |

Order example

| Ordering option | Code | Description |
|---------------------------|------|--|
| 1 Type | C67 | Diaphragm valve, manually operated, plastic handwheel, seal adjuster |
| 2 Position of space saver | Z | Space Saver for Z position |
| 3 Connection size | 8 | 1/2", international code: 8 |
| 4 Body configuration | D | 2/2-way body |
| 5 Connection type | 75 | Flare connection with PVDF union nut |
| 6 Valve body material | 30 | PFA, perfluoroalkoxy |
| 7 Diaphragm material | 54 | PTFE/EPDM one-piece |
| 8 Control function | 0 | Manually operated |
| 9 Actuator version | 2 | Actuator size 2 |
| 10 Design | | Without |
| 11 High Purity version | HPW | High purity white |

Order data - body configuration - T body (code T)

Order codes

The order data provide an overview of standard configurations.

Please check the availability before ordering. Other configurations available on request.

| 1 Type | Code |
|--|------|
| Diaphragm valve, manually operated, plastic handwheel, seal adjuster | C67 |

| 2 Position of space saver | Code |
|----------------------------|------|
| Without | |
| Space Saver for Y position | Y |

| 3 Connection size | Code |
|--------------------------------|------|
| Position Y | |
| 1/4", international code: 4 | 4 |
| 3/8", international code: 6 | 6 |
| 1/2", international code: 8 | 8 |
| 3/4", international code: 12 | 12 |
| 1", international code: 16 | 16 |
| 1 1/4", international code: 20 | 20 |

| 4 Body configuration | Code |
|----------------------|------|
| T-body | T |

| 5 Connection type | Code |
|---|------|
| Tube | |
| Flare connection with CPFA union nut | 73 |
| Flare connection with PVDF union nut | 75 |
| Flare connection with PFA union nut | 77 |
| Pipe | |
| Spigot – inch, for welding or solvent cementing, depending on the body material | 30 |

| 6 Valve body material | Code |
|-----------------------|------|
| PFA, perfluoroalkoxy | 30 |

| 7 Diaphragm material | Code |
|----------------------|------|
| PTFE/EPDM one-piece | 54 |

| 8 Control function | Code |
|--------------------|------|
| Manually operated | 0 |

| 9 Actuator version | Code |
|---------------------------------------|------|
| Standard version | |
| Actuator size 1 | 1 |
| Actuator size 2 | 2 |
| Actuator size 3 | 3 |
| Standard version with ECTFE union nut | |
| Actuator size 1, with ECTFE union nut | 1E |
| Actuator size 2, with ECTFE union nut | 2E |

| 9 Actuator version | Code |
|---------------------------------------|------|
| Actuator size 3, with ECTFE union nut | 3E |

| 10 Position of space saver-2 | Code |
|-------------------------------|------|
| Space Saver for X position | X |
| Space Saver for Z position | Z |
| Space Saver for X+ Z position | S |

| 11 Connection size 2 | Code |
|----------------------------------|------|
| Position X and Z | |
| 1/4", international code: 4 | 4 |
| 3/8", international code-2: 6 | 6 |
| 1/2", international code-2: 8 | 8 |
| 3/4", international code-2: 12 | 12 |
| 1", international code-2: 16 | 16 |
| 1 1/4", international code-2: 20 | 20 |

| 12 Connection type spigot 2 | Code |
|---|------|
| Tube | |
| Spigot – inch, for welding or solvent cementing, depending on the body material | 30 |
| Flare connection with CPFA union nut | 73 |
| Flare connection with PVDF union nut | 75 |
| Pipe | |
| Flare connection with PFA union nut | 77 |

| 13 Design | Code |
|-----------|------|
| Without | |

| 14 High Purity version | Code |
|------------------------|------|
| High purity white | HPW |

Order example

| Ordering option | Code | Description |
|------------------------------|------|--|
| 1 Type | C67 | Diaphragm valve, manually operated, plastic handwheel, seal adjuster |
| 2 Position of space saver | Y | Space Saver for Y position |
| 3 Connection size | 8 | 1/2", international code: 8 |
| 4 Body configuration | T | T-body |
| 5 Connection type | 75 | Flare connection with PVDF union nut |
| 6 Valve body material | 30 | PFA, perfluoroalkoxy |
| 7 Diaphragm material | 54 | PTFE/EPDM one-piece |
| 8 Control function | 0 | Manually operated |
| 9 Actuator version | 2 | Actuator size 2 |
| 10 Position of space saver-2 | Z | Space Saver for Z position |
| 11 Connection size 2 | 8 | 1/2", international code-2: 8 |
| 12 Connection type spigot 2 | 75 | Flare connection with PVDF union nut |
| 13 Design | | Without |
| 14 High Purity version | HPW | High purity white |

Technical data C67 PFA

Medium

Working medium: Corrosive, inert, gaseous and liquid media – in particular high-purity media – which have no negative impact on the physical and chemical properties of the body and diaphragm material.

Temperature

Media temperature: PFA valve body material (code 30): -10 – 150 °C
Observe pressure/temperature diagram

Ambient temperature: 0 – 60 °C


Storage temperature: 0 – 40 °C

Pressure

Operating pressure: 0 – 6 bar

Pressure/temperature diagram:

Valve body material PFA (code 30)



Note: The temperature/pressure diagram is only an aid. The data refers to water as a working medium. A change of operating conditions or other media may result in deviations. In case of doubt, it is advisable to test the behaviour of the material under the definitive operating conditions in a test installation.
Temperatures below 0 °C can have a negative influence on the actuation speed.

Cv values:

Body configuration - 2/2-way body (code D)

| Actuator size (code) | Connection size | Connection | |
|-------------------------|-----------------|-----------------|-----------------|
| | | On both sides | |
| | X, Z | Tube connection | Pipe connection |
| 1, 1E | 1/4" | 4.0 | 15.0 |
| | 3/8" | 15.0 | - |
| 2, 2E | 1/2" | 35.0 | 68.0 |
| | 3/4" | 68.0 | 68.0 |
| 3, 3E | 3/4" | 68.0 | 126.0 |
| | 1" | 158.0 | 175.0 |
| | 1 1/4" | 170.0 | - |
| 4 | 1 1/2 " | - | 1225.0 |
| | 2" | - | 1225.0 |

Kv values in l/min

If the 2/2-way body has a tube and pipe connection, the Kv values of the tube connection are used.

Cv values:**Body configuration - 2/2-way body (code D) – High Flow design**

| Actuator size (code) | Connection size | Connection | |
|-------------------------|-----------------|-----------------|-----------------|
| | | On both sides | |
| | X, Z | Tube connection | Pipe connection |
| 2 F, 2EF | 1/2" | - | 115.0 |
| | 3/4" | 115.0 | 115.0 |
| | 1" | 123.0 | 123.0 |
| 3 F, 3EF | 1" | 316.0 | 316.0 |
| | 1¼" | 325.0 | - |

Kv values in l/min

Body configuration – 2/2-way body (code D) – Nexus Connect® connection type (code NX)

| Actuator size (code) | Connection size | Connection | |
|-------------------------|-----------------|---------------|------------|
| | | On both sides | |
| | X, Z | Welded | SpaceSaver |
| 1 | 1/4" | 7.82 | - |
| | 3/8" | 13.0 | 13.3 |
| 2 | 1/2" | 48.1 | 35.2 |
| | 3/4" | 66.3 | - |
| 2F | 3/4" | - | 110.0 |
| 3 | 1" | 142.0 | - |
| 3F | 1" | - | 255.0 |

Kv values in l/min

Cv values:**Body configuration - T body (code T)**

| Actuator size (code) | Connection size | | Connection | | |
|-------------------------|-----------------|----------|---|----------------------|---------------------------|
| | | | On both sides at main pipe (X, Z) and branch (Y) | | One side |
| | Main pipe X, Z | Branch Y | Tube connec- tion | Pipe connec- tion | Pipe/tube con- nection |
| 1, 1E | 1/4" | 1/4" | - | 17.0 | - |
| | 3/8" | 1/4" | 4.0 | - | - |
| | 3/8" | 3/8" | 13.0 | - | - |
| | 1/2" | 1/4" | - | 18.0 | - |
| | 1/2" | 3/8" | 17.0 | - | - |
| | 3/4" | 3/8" | 18.0 | - | - |
| 2, 2E | 1/2" | 1/2" | 28.0 | 62.0 | 36.0 |
| | 3/4" | 1/4" | - | 35.0 | - |
| | 3/4" | 1/2" | 35.0 | 38.0 | 38.0 |
| | 3/4" | 3/4" | 62.0 | 71.0 | - |
| | 1" | 1/2" | 38.0 | 101.0 | - |
| | 1" | 3/4" | 71.0 | - | - |
| 3, 3E | 1" | 1" | 137.0 | 135.0 | 145.0 |
| | 1" | 1/2" | - | 101.0 | 42.0 |
| | 1" | 3/4" | - | 130.0 | - |
| | 1 1/4" | 1/2" | 53.0 | - | - |
| | 1 1/4" | 3/4" | 117.0 | - | - |
| | 1 1/4" | 1" | 150.0 | - | - |
| | 1 1/4" | 1 1/4" | 170.0 | - | - |

At branch Y

Kv values in l/min

Vacuum:

400 mbar absolute

The service life of the valve may be affected if exposed to a greater vacuum or when valves are installed on the pump suction side.

Product conformities

Machinery Directive: 2006/42/EC

Food: FDA

EAC: The product is certified according to EAC.


Mechanical data

Flow direction: Optional

Dimensions C67 PFA

2/2-way valves (code D)

Flare connection (code 73, 75, 77)



| Actuator size ¹⁾ | Connection size | Pos. Space Saver ²⁾ | ØB | ØB1 | H | H1 | L | L1 | L2 |
|-----------------------------|-----------------|--------------------------------|------|------|-------|------|-------|-------|-------|
| 1, 1E | 1/4" | - | 51.4 | 31.5 | 91.5 | 13.6 | 112.8 | 56.4 | 56.4 |
| 1, 1E | 1/4" | Z | 51.4 | 31.5 | 91.5 | 13.6 | 120.1 | 56.4 | 63.7 |
| 1, 1E | 3/8" | - | 51.4 | 31.5 | 91.5 | 13.6 | 114.0 | 57.0 | 57.0 |
| 1, 1E | 3/8" | Z | 51.4 | 31.5 | 91.5 | 13.6 | 119.4 | 57.0 | 62.4 |
| 2, 2E | 1/2" | K | 64.0 | 60.0 | 109.0 | 19.0 | 133.4 | 65.9 | 67.5 |
| 2, 2E | 1/2" | - | 64.0 | 60.0 | 109.0 | 16.0 | 131.8 | 65.9 | 65.9 |
| 2, 2E | 1/2" | S | 64.0 | 60.0 | 109.0 | 16.0 | 142.0 | 71.0 | 71.0 |
| 2, 2E | 1/2" | Z | 64.0 | 60.0 | 109.0 | 16.0 | 136.9 | 65.9 | 71.0 |
| 2, 2E | 3/4" | K | 64.0 | 60.0 | 109.0 | 19.0 | 134.4 | 66.9 | 67.5 |
| 2, 2E | 3/4" | - | 64.0 | 60.0 | 109.0 | 19.0 | 133.8 | 66.9 | 66.9 |
| 3, 3E | 3/4" | K | 80.0 | 90.0 | 166.5 | 25.0 | 165.8 | 82.9 | 82.9 |
| 2, 2E | 3/4" | S | 64.0 | 60.0 | 109.0 | 19.0 | 156.8 | 78.4 | 78.4 |
| 2, 2E | 3/4" | Z | 64.0 | 60.0 | 109.0 | 19.0 | 145.3 | 66.9 | 78.4 |
| 3, 3E | 3/4" | - | 80.0 | 90.0 | 166.5 | 25.0 | 165.8 | 82.9 | 82.9 |
| 3, 3E | 1" | K | 80.0 | 90.0 | 166.5 | 25.0 | 172.5 | 89.5 | 83.0 |
| 3, 3E | 1" | - | 80.0 | 90.0 | 166.5 | 25.0 | 179.0 | 89.5 | 89.5 |
| 3, 3E | 1" | S | 80.0 | 90.0 | 166.5 | 25.0 | 198.8 | 99.4 | 99.4 |
| 3, 3E | 1" | Z | 80.0 | 90.0 | 166.5 | 25.0 | 188.9 | 89.5 | 99.4 |
| 3, 3E | 1¼" | - | 80.0 | 90.0 | 166.5 | 25.0 | 238.4 | 119.2 | 119.2 |
| 2 F, 2EF | 3/4" | - | 64.0 | 60.0 | 109.0 | 19.0 | 133.8 | 66.9 | 66.9 |
| 2 F, 2EF | 3/4" | S | 64.0 | 60.0 | 109.0 | 19.0 | 156.8 | 78.4 | 78.4 |
| 2 F, 2EF | 3/4" | Z | 64.0 | 60.0 | 109.0 | 19.0 | 145.3 | 66.9 | 78.4 |
| 2 F, 2EF | 1" | - | 64.0 | 60.0 | 109.0 | 19.0 | 160.0 | 80.0 | 80.0 |
| 3 F, 3EF | 1" | - | 80.0 | 90.0 | 166.5 | 25.0 | 179.0 | 89.5 | 89.5 |
| 3 F, 3EF | 1" | S | 80.0 | 90.0 | 166.5 | 25.0 | 198.8 | 99.4 | 99.4 |
| 3 F, 3EF | 1" | Z | 80.0 | 90.0 | 166.5 | 25.0 | 188.9 | 89.5 | 99.4 |

| Actuator size ¹⁾ | Connection size | Pos. Space Saver ²⁾ | ØB | ØB1 | H | H1 | L | L1 | L2 |
|-----------------------------|-----------------|--------------------------------|------|------|-------|------|-------|-------|-------|
| 3 F, 3EF | 1¼" | - | 80.0 | 90.0 | 166.5 | 25.0 | 238.4 | 119.2 | 119.2 |


Dimensions in mm

1) **Actuator version**

- Code 1: Actuator size 1
- Code 1E: Actuator size 1, with ECTFE union nut
- Code 2: Actuator size 2
- Code 2 F: Actuator size 2 High Flow
- Code 2E: Actuator size 2, with ECTFE union nut
- Code 2EF: Actuator size 2 High Flow, with ECTFE union nut
- Code 3: Actuator size 3
- Code 3 F: Actuator size 3 High Flow
- Code 3E: Actuator size 3, with ECTFE union nut
- Code 3EF: Actuator size 3 High Flow, with ECTFE union nut

2) **Position of space saver**

- Code K: Flare connection in position X, butt weld spigot in position Z
- Code S: Space Saver for X+ Z position
- Code Z: Space Saver for Z position

Butt weld spigot (code 30)

| Actuator size ¹⁾ | Connec-tion size | Pos. Space Saver ²⁾ | ØB | ØB1 | H | H1 | L | L1 | L2 | Spigot (A) | |
|-----------------------------|------------------|--------------------------------|-------|-------|-------|------|-------|-------|-------|------------|------|
| | | | | | | | | | | ød | ød1 |
| 1, 1E | 1/4" | - | 51.4 | 31.5 | 91.5 | 13.6 | 102.0 | 51.0 | 51.0 | 13.7 | 9.2 |
| 2, 2E | 1/2" | - | 64.0 | 60.0 | 109.0 | 19.0 | 135.0 | 67.5 | 67.5 | 21.3 | 15.8 |
| 2, 2E | 3/4" | - | 64.0 | 60.0 | 109.0 | 19.0 | 135.0 | 67.5 | 67.5 | 26.7 | 20.3 |
| 3, 3E | 3/4" | - | 80.0 | 90.0 | 166.5 | 25.0 | 166.0 | 83.0 | 83.0 | 26.7 | 20.3 |
| 3, 3E | 1" | - | 80.0 | 90.0 | 166.5 | 25.0 | 166.0 | 83.0 | 83.0 | 33.4 | 26.6 |
| 4 | 1½" | - | 132.3 | 140.0 | 197.8 | 40.0 | 194.0 | 97.0 | 97.0 | 48.3 | 40.9 |
| 4 | 2" | - | 132.3 | 140.0 | 197.8 | 40.0 | 224.0 | 112.0 | 112.0 | 60.3 | 52.3 |
| High Flow | | | | | | | | | | | |
| 2 F, 2EF | 1/2" | - | 64.0 | 60.0 | 109.0 | 19.0 | 135.0 | 67.5 | 67.5 | 21.3 | 15.8 |
| 2 F, 2EF | 3/4" | - | 64.0 | 60.0 | 109.0 | 19.0 | 135.0 | 67.5 | 67.5 | 26.7 | 20.3 |
| 2 F, 2EF | 1" | - | 64.0 | 60.0 | 109.0 | 19.0 | 148.0 | 74.0 | 74.0 | 33.4 | 26.6 |
| 3 F, 3EF | 1" | - | 80.0 | 90.0 | 166.5 | 25.0 | 166.0 | 83.0 | 83.0 | 33.4 | 26.6 |

Dimensions in mm

1) **Actuator version**

Code 1: Actuator size 1

Code 1E: Actuator size 1, with ECTFE union nut

Code 2: Actuator size 2

Code 2 F: Actuator size 2 High Flow

Code 2E: Actuator size 2, with ECTFE union nut

Code 2EF: Actuator size 2 High Flow, with ECTFE union nut

Code 3: Actuator size 3

Code 3 F: Actuator size 3 High Flow

Code 3E: Actuator size 3, with ECTFE union nut

Code 3EF: Actuator size 3 High Flow, with ECTFE union nut

Code 4: Actuator size 4


2) **Position of space saver**

Code K: Flare connection in position X, butt weld spigot in position Z

Code S: Space Saver for X+ Z position

Code Z: Space Saver for Z position

PrimeLock® connection (code PL)



| Actuator size ¹⁾ | Connection size | Pos. Space Saver ²⁾ | ØB | ØB1 | H | H1 | L | L1 | L2 |
|-----------------------------|-----------------|--------------------------------|------|------|-------|------|-------|-------|-------|
| 1, 1E | 1/4" | - | 51.4 | 31.5 | 91.5 | 15.0 | 113.0 | 57.0 | 57.0 |
| 1, 1E | 3/8" | - | 51.4 | 31.5 | 91.5 | 15.0 | 117.0 | 59.0 | 59.0 |
| 2, 2E | 1/2" | - | 64.0 | 60.0 | 109.0 | 16.0 | 141.0 | 71.0 | 71.0 |
| 2 F, 2EF | 3/4" | - | 64.0 | 60.0 | 109.0 | 19.0 | 156.0 | 79.0 | 79.0 |
| 2 F, 2EF | 1" | - | 64.0 | 60.0 | 109.0 | 19.0 | 169.0 | 85.0 | 85.0 |
| 3 F, 3EF | 1" | - | 80.0 | 90.0 | 166.5 | 25.0 | 150.5 | 94.0 | 94.0 |
| 3 F, 3EF | 1 1/4" | - | 80.0 | 90.0 | 166.5 | 25.0 | 150.5 | 105.0 | 105.0 |

Dimensions in mm

1) Actuator version

Code 1: Actuator size 1

Code 1E: Actuator size 1, with ECTFE union nut

Code 2: Actuator size 2

Code 2 F: Actuator size 2 High Flow

Code 2E: Actuator size 2, with ECTFE union nut

Code 2EF: Actuator size 2 High Flow, with ECTFE union nut

Code 3: Actuator size 3

Code 3 F: Actuator size 3 High Flow

Code 3E: Actuator size 3, with ECTFE union nut


Code 3EF: Actuator size 3 High Flow, with ECTFE union nut

2) Position of space saver

Code K: Flare connection in position X, butt weld spigot in position Z

Code S: Space Saver for X+ Z position

Code Z: Space Saver for Z position

Tube spigot (code T3)

| Actuator size ¹⁾ | Connec-tion size | Pos. Space Saver ²⁾ | ØB | ØB1 | H | $H1$ | L | $L1$ | $L2$ | Spigot (A) | |
|-----------------------------|------------------|--------------------------------|-------------|--------------|-------|-------|-------|------|------|-------------|--------------|
| | | | | | | | | | | Ød | Ød1 |
| 1, 1E | 3/8" | - | 51.4 | 31.5 | 107.0 | 13.6 | 106.0 | 53.0 | 53.0 | 9.5 | 6.6 |
| 2, 2E | 1/2" | - | 64.0 | 60.0 | 120.5 | 16.0 | 122.0 | 61.0 | 61.0 | 12.7 | 9.7 |
| 2, 2E | 3/4" | - | 64.0 | 60.0 | 126.5 | 19.0 | 135.0 | 67.5 | 67.5 | 19.05 | 15.9 |
| 3, 3E | 1" | - | 80.0 | 90.0 | 165.8 | 150.5 | 25.0 | 82.5 | 82.5 | 25.4 | 22.2 |
| 2 F, 2EF | 3/4" | - | 64.0 | 60.0 | 126.5 | 19.0 | 135.0 | 67.5 | 67.5 | 19.05 | 15.9 |
| 2 F, 2EF | 1" | - | 64.0 | 60.0 | 126.5 | 19.0 | 148.0 | 74.0 | 74.0 | 25.4 | 22.2 |
| 3 F, 3EF | 1" | - | 80.0 | 90.0 | 165.0 | 150.5 | 25.0 | 82.5 | 82.5 | 25.4 | 22.2 |
| 3 F, 3EF | 1 1/4" | - | 80.0 | 90.0 | 176.0 | 150.5 | 25.0 | 88.0 | 88.0 | 31.75 | 28.2 |

Dimensions in mm

1) **Actuator version**

Code 1: Actuator size 1

Code 1E: Actuator size 1, with ECTFE union nut

Code 2: Actuator size 2

Code 2 F: Actuator size 2 High Flow

Code 2E: Actuator size 2, with ECTFE union nut

Code 2EF: Actuator size 2 High Flow, with ECTFE union nut

Code 3: Actuator size 3

Code 3 F: Actuator size 3 High Flow

Code 3E: Actuator size 3, with ECTFE union nut


Code 3EF: Actuator size 3 High Flow, with ECTFE union nut

2) **Position of space saver**

Code K: Flare connection in position X, butt weld spigot in position Z

Code S: Space Saver for X+ Z position

Code Z: Space Saver for Z position

Nexus Connect® (code NX)**Nexus Connect®, welded**

| Actuator size ¹⁾ | Connection size | Pos. Space Saver ²⁾ | ØB | ØB1 | H | H1 | L | L1 | L2 |
|-----------------------------|-----------------|--------------------------------|------|------|-------|------|-------|-------|-------|
| 1 | 1/4" | - | 51.4 | 38.0 | 91.5 | 13.6 | 140.5 | 70.3 | 70.3 |
| 1 | 3/8" | - | 51.4 | 38.0 | 91.5 | 13.6 | 147.7 | 73.9 | 73.9 |
| 2 | 1/2" | - | 64.0 | 64.7 | 109.0 | 19.0 | 153.0 | 76.5 | 76.5 |
| 2 | 3/4" | - | 64.0 | 64.7 | 109.0 | 19.0 | 179.1 | 89.6 | 89.6 |
| 3 | 1" | - | 80.0 | 86.0 | 150.5 | 25.0 | 205.0 | 102.5 | 102.5 |

Nexus Connect®, SpaceSaver

| Actuator size ¹⁾ | Connection size | Pos. Space Saver ²⁾ | ØB | ØB1 | H | H1 | L | L1 | L2 |
|-----------------------------|-----------------|--------------------------------|------|------|-------|------|-------|------|------|
| 1 | 3/8" | X, Z | 51.4 | 38.0 | 91.5 | 13.6 | 112.4 | 56.2 | 56.2 |
| 2 | 1/2" | X, Z | 64.0 | 64.7 | 109.0 | 16.0 | 131.6 | 65.8 | 65.8 |
| 2F | 3/4" | X, Z | 64.0 | 64.7 | 109.0 | 19.0 | 145.1 | 72.6 | 72.6 |
| 3F | 1" | X, Z | 80.0 | 86.0 | 150.5 | 25.0 | 176.3 | 88.2 | 88.2 |


Dimensions in mm

1) **Actuator version**

- Code 1: Actuator size 1
- Code 2: Actuator size 2
- Code 2 F: Actuator size 2 High Flow
- Code 3: Actuator size 3
- Code 3 F: Actuator size 3 High Flow

2) **Position of space saver**

- Code X: Space Saver for X position
- Code Z: Space Saver for Z position

T body (code T)**Flare connection (code 73, 75, 77)**

| Actuator size ¹⁾ | Connection size | | Pos. Space Saver ²⁾ | | $\varnothing B$ | $\varnothing B1$ | H | $H1$ | $H2$ | L | $L1$ | $L2$ | $L3$ | $L4$ |
|-----------------------------|-----------------|----------|--------------------------------|----------|-----------------|------------------|-------|------|------|-------|-------|-------|-------|-------|
| | Pos. (X, Z) | Pos. (Y) | Pos. (X, Z) | Pos. (Y) | | | | | | | | | | |
| 1, 1E | 3/8" | 1/4" | - | - | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 115.0 | 57.5 | 57.5 | 67.4 | 84.4 |
| 1, 1E | 3/8" | 3/8" | - | - | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 115.0 | 57.5 | 57.5 | 68.0 | 85.0 |
| 1, 1E | 1/2" | 3/8" | - | - | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 120.8 | 60.4 | 60.4 | 68.0 | 85.0 |
| 1, 1E | 1/2" | 3/8" | Z | - | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 131.9 | 60.4 | 71.5 | 68.0 | 85.0 |
| 1, 1E | 3/4" | 3/8" | - | - | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 125.8 | 62.9 | 62.9 | 68.0 | 85.0 |
| 1, 1E | 3/4" | 3/8" | X | - | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 135.3 | 72.4 | 62.9 | 68.0 | 85.0 |
| 1, 1E | 3/4" | 3/8" | Z | - | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 135.3 | 62.9 | 72.4 | 68.0 | 85.0 |
| 2, 2E | 1/2" | 1/2" | - | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 131.8 | 65.9 | 65.9 | 80.4 | 98.4 |
| 2, 2E | 1/2" | 1/2" | Z | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 136.0 | 65.9 | 70.1 | 80.4 | 98.4 |
| 2, 2E | 1/2" | 1/2" | - | Y | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 131.8 | 65.9 | 65.9 | 85.5 | 103.5 |
| 2, 2E | 3/4" | 1/2" | - | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 133.8 | 66.9 | 66.9 | 80.4 | 98.4 |
| 2, 2E | 3/4" | 1/2" | S | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 156.8 | 78.4 | 78.4 | 80.4 | 98.4 |
| 2, 2E | 3/4" | 1/2" | X | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 145.3 | 78.4 | 66.9 | 80.4 | 98.4 |
| 2, 2E | 3/4" | 1/2" | Z | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 145.3 | 66.9 | 78.4 | 80.4 | 98.4 |
| 2, 2E | 3/4" | 1/2" | - | Y | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 133.8 | 66.9 | 66.9 | 85.5 | 103.5 |
| 2, 2E | 3/4" | 3/4" | - | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 133.8 | 66.9 | 66.9 | 81.4 | 99.4 |
| 2, 2E | 3/4" | 3/4" | X | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 145.3 | 78.4 | 66.9 | 81.4 | 99.4 |
| 2, 2E | 3/4" | 3/4" | Z | - | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 145.3 | 66.9 | 78.4 | 81.4 | 99.4 |
| 2, 2E | 3/4" | 3/4" | - | Y | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 133.8 | 66.9 | 66.9 | 92.4 | 110.4 |
| 3, 3E | 1" | 1" | - | - | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 168.0 | 84.0 | 84.0 | 110.5 | 133.0 |
| 3, 3E | 1" | 1" | X | - | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 177.9 | 93.9 | 84.0 | 110.5 | 133.0 |
| 3, 3E | 1" | 1" | Z | - | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 177.9 | 84.0 | 93.9 | 110.5 | 133.0 |
| 3, 3E | 1 1/4" | 1/2" | - | - | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 238.4 | 119.2 | 119.2 | 99.9 | 122.4 |
| 3, 3E | 1 1/4" | 1" | - | - | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 238.4 | 119.2 | 119.2 | 110.5 | 133.0 |
| 3, 3E | 1 1/4" | 1 1/4" | - | - | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 238.4 | 119.2 | 143.2 | 165.7 | |

| Actuator size ¹⁾ | Connection size | | Pos. Space Saver ²⁾ | | ØB | ØB1 | H | H1 | H2 | L | L1 | L2 | L3 | L4 |
|-----------------------------|-----------------|----------|--------------------------------|----------|------|------|-------|------|------|-------|------|------|------|-------|
| | Pos. (X, Z) | Pos. (Y) | Pos. (X, Z) | Pos. (Y) | | | | | | | | | | |
| 2 F, 2EF | 1" | 1/2" | - | - | 64.0 | 60.0 | 135.9 | 25.0 | 28.5 | 154.0 | 77.0 | 77.0 | 81.4 | 100.9 |
| 2 F, 2EF | 1" | 1/2" | S | - | 64.0 | 60.0 | 135.9 | 25.0 | 28.5 | 163.8 | 81.9 | 81.9 | 81.4 | 100.9 |
| 2 F, 2EF | 1" | 1/2" | X | - | 64.0 | 60.0 | 135.9 | 25.0 | 28.5 | 158.9 | 81.9 | 77.0 | 81.4 | 100.9 |
| 2 F, 2EF | 1" | 1/2" | Z | - | 64.0 | 60.0 | 135.9 | 25.0 | 28.5 | 158.9 | 77.0 | 81.9 | 81.4 | 100.9 |
| 2 F, 2EF | 1" | 3/4" | - | - | 64.0 | 60.0 | 135.9 | 25.0 | 28.5 | 154.0 | 77.0 | 77.0 | 82.4 | 101.9 |
| 2 F, 2EF | 1" | 3/4" | X | - | 64.0 | 60.0 | 135.9 | 25.0 | 28.5 | 158.9 | 81.9 | 77.0 | 82.4 | 101.9 |
| 2 F, 2EF | 1" | 3/4" | Z | - | 64.0 | 60.0 | 135.9 | 25.0 | 28.5 | 158.9 | 77.0 | 81.9 | 82.4 | 101.9 |
| 2 F, 2EF | 1" | 3/4" | - | Y | 64.0 | 60.0 | 135.9 | 19.0 | 28.5 | 154.0 | 77.0 | 77.0 | 92.9 | 112.4 |

Dimensions in mm

1) **Actuator version**

Code 1: Actuator size 1

Code 1E: Actuator size 1, with ECTFE union nut

Code 2: Actuator size 2

Code 2 F: Actuator size 2 High Flow

Code 2E: Actuator size 2, with ECTFE union nut

Code 2EF: Actuator size 2 High Flow, with ECTFE union nut

Code 3: Actuator size 3

Code 3 F: Actuator size 3 High Flow

Code 3E: Actuator size 3, with ECTFE union nut


Code 3EF: Actuator size 3 High Flow, with ECTFE union nut

2) **Position of space saver**

Code X: Space Saver for X position

Code Y: Space Saver for Y position

Code Z: Space Saver for Z position

Butt weld spigot (code 30)

Dimensions Spigot (A) (see "Butt weld spigot (code 30)", page 24)

| Actuator size ¹⁾ | Connection size | | Pos. Space Saver ²⁾ | Con-nection ³⁾ | ØB | ØB1 | H | H1 | H2 | L | L1 | L2 | L3 | L4 |
|-----------------------------|-----------------|----------|--------------------------------|---------------------------|------|------|-------|------|------|-------|------|------|-------|-------|
| | Pos. (X, Z) | Pos. (Y) | | | | | | | | | | | | |
| 1, 1E | 1/4" | 1/4" | - | 73, 75, 77 | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 106.0 | 53.0 | 53.0 | 63.5 | 80.5 |
| 1, 1E | 1/4" | 1/2" | - | 30 | 51.4 | 31.5 | 114.5 | 19.0 | 23.0 | 106.0 | 53.0 | 53.0 | 63.5 | 80.5 |
| 2, 2E | 1/2" | 1/2" | - | 30 | 64.0 | 60.0 | 126.5 | 19.0 | 19.0 | 122.0 | 61.0 | 61.0 | 75.54 | 93.5 |
| 2, 2E | 1/4" | 3/4" | - | 30 | 64.0 | 60.0 | 135.9 | 25.0 | 28.5 | 140.0 | 70.0 | 70.0 | 76.5 | 96.0 |
| 3, 3E | 1/2" | 1" | - | 30 | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 163.0 | 81.5 | 81.5 | 102.0 | 124.5 |
| 3, 3E | 1/2" | 1" | - | 73, 75, 77 | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 163.0 | 81.5 | 81.5 | 99.9 | 122.4 |
| 3, 3E | 3/4" | 1" | - | 30 | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 163.0 | 81.5 | 81.5 | 102.0 | 124.5 |
| 3, 3E | 1" | 1" | - | 30 | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 163.0 | 81.5 | 81.5 | 103.5 | 126.0 |
| 3, 3E | 1" | 1" | - | 73, 75, 77 | 80.0 | 90.0 | 166.5 | 25.0 | 25.0 | 163.0 | 81.5 | 81.5 | 110.5 | 133.0 |

Dimensions in mm

1) **Actuator version**

Code 1: Actuator size 1

Code 1E: Actuator size 1, with ECTFE union nut

Code 2: Actuator size 2

Code 2 F: Actuator size 2 High Flow

Code 2E: Actuator size 2, with ECTFE union nut

Code 2EF: Actuator size 2 High Flow, with ECTFE union nut

Code 3: Actuator size 3

Code 3 F: Actuator size 3 High Flow

Code 3E: Actuator size 3, with ECTFE union nut

Code 3EF: Actuator size 3 High Flow, with ECTFE union nut

2) **Position of space saver**

Code X: Space Saver for X position

Code Y: Space Saver for Y position

Code Z: Space Saver for Z position

3) **Connection type**

Code 30: Spigot – inch, for welding or solvent cementing, depending on the body material


Code 73: Flare connection with CPFA union nut

Code 75: Flare connection with PVDF union nut


Code 77: Flare connection with PFA union nut

Mounting dimensions

2/2-way valve (code D)



T valve (code T)



2/2-way valves (code D)

| Actuator size | Ød | A | B | C |
|-----------------|-----|-------|-------|------|
| 1, 1E | 5.5 | 50.5 | 25.25 | 33.5 |
| 2, 2E, 2 F, 2EF | 5.5 | 61.5 | 31.0 | 40.0 |
| 3, 3E, 3 F, 3EF | 6.5 | 78.0 | 39.0 | 56.0 |
| 4 | 9.0 | 124.0 | 62.0 | 94.0 |


Dimensions in mm

T valve (code T)

| Actuator size | Ød | A | B | C |
|-----------------|-----|------|------|------|
| 1, 1E | 5.5 | 44.3 | 27.3 | 50.0 |
| 2, 2E, 2 F, 2EF | 5.5 | 61.5 | 43.5 | 41.5 |
| 3, 3E, 3 F, 3EF | 6.5 | 79.5 | 57.0 | 52.5 |

Dimensions in mm

Mounting holes, round and slotted hole



Actuator size 1-3

 $d = 6.0$ $d1 = 12.0$

Actuator size 4

 $d = 9.0$ $d1 = 19.0$

Dimensions in mm

Dear customers,

In order to simplify installation, we are switching over the mounting holes to slotted holes for all valve sizes.

Due to the gradual changeover in manufacturing, you may therefore receive valve bodies with new slotted holes and also with the old, round boreholes during this phase.

We ask for your understanding in this matter.

GEMÜ C67 CleanStar PFA 3/5-way

Manually operated 3/5-way diaphragm valve with PFA valve body



Features

- High flow rate
- Minimal contamination
- Minimal deadleg
- Optional flow direction
- Can be used as a media mixing configuration or manifold valve
- Both actuators can be independently controlled
- Combination of manual and pneumatic actuator selectable

Description

The ultra pure GEMÜ C67 CleanStar® 3/5-way diaphragm valve with a V valve body made of PFA has two valve seats. All media wetted parts are made of PFA or PTFE (diaphragm). The external actuator parts are made of PVDF. Solid mounting lugs, as well as a leak detection hole are integrated as standard. The union nuts are available in PVDF, PFA and C-PFA. This High Purity version of the CleanStar series complies with the strictest purity standards and boasts high chemical resistance. It can also be used with high media temperatures. As such, it is often used at the supply and distribution level in semiconductor factories, particularly to collect or mix media flows.

Technical specifications

- **Media temperature :** -10 to 150 °C
- **Ambient temperature:** 0 to 60 °C
- **Operating pressure :** 0 to 6 bar
- **Nominal sizes:** DN 10 to 15
- **Body configurations:** V valve body
- **Connection types:** Flare | Flare SpaceSaver
- **Connection standards:** DIN
- **Body materials:** PFA
- **Diaphragm materials:** PTFE/EPDM
- **Conformities:** EAC | FDA | TA Luft (German Clean Air Act)


Technical data depends on the respective configuration

Availability C67 PFA 3/5-way

Connections

| Actuator size | Flare connection | SpaceSaver position | | | | | Butt weld spigot |
|---------------|------------------|-------------------------|------------|------------|------------|------------|------------------|
| | | Connection size X, Y, Z | None | X (code X) | Y (code Y) | Z (code Z) | |
| | | | Code | | | | |
| 2 | 8 | X | On request |
| | 12 | X | On request |

Actuator assignments



| V1 | | V2 | | Control function (code) | |
|--------------------------|----------------------|--------------------------|----------------------|-------------------------|--|
| Valve 1 (position X - Y) | | Valve 2 (position Z - Y) | | | |
| Type | Control function | Type | Control function | | |
| C60 | Normally closed (NC) | C60 | Normally closed (NC) | 1 | |
| C60 | Normally closed (NC) | C60 | Normally open (NO) | D | |
| C60 | Normally closed (NC) | C67 | Manually operated | F | |
| C60 | Normally open (NO) | C60 | Normally open (NO) | 2 | |
| C60 | Normally open (NO) | C60 | Normally closed (NC) | G | |
| C60 | Normally open (NO) | C67 | Manually operated | K | |
| C60 | Normally open (NO) | C60 | Double acting | H | |
| C67 | Manually operated | C60 | Normally closed (NC) | A | |
| C67 | Manually operated | C60 | Normally open (NO) | B | |
| C67 | Manually operated | C67 | Manually operated | 0 | |

Order data C67 PFA 3/5-way

Order codes

The order data provide an overview of standard configurations.

Please check the availability before ordering. Other configurations available on request.

Provisionally only designs with the same nominal sizes in all positions

| 1 Type | Code | 8 Control function | Code |
|--|------|--|------|
| C60 - valve 1 (between X - Y) | | Normally open, double acting | H |
| Diaphragm valve, pneumatically operated, plastic piston actuator, optical position indicator, stroke limiter (for actuator size 1–3 only) | C60 | C60 / C67 | |
| C67 - valve 1 (between X - Y) | C67 | Normally closed, manually operated | F |
| Diaphragm valve, manually operated, plastic handwheel, seal adjuster | | Normally open, manually operated | K |
| 2 Position of space saver | Code | C67 / C60 | |
| Without | | Manually operated, normally closed | A |
| Space Saver for X+ Z position | S | C67 / C67 | |
| Space Saver for X position | X | Manually operated | 0 |
| Space Saver for Y position | Y | 3 | |
| Space Saver for Z position | Z | Standard version | |
| 3 Connection size | Code | Actuator size 2 | 2 |
| Position Y | | Standard version with ECTFE union nut | |
| 1/2", international code: 8 | 8 | Actuator size 2, with ECTFE union nut | 2E |
| 3/4", international code: 12 | 12 | 4 | |
| 4 Body configuration | Code | 10 Design | Code |
| Multi-port body V-form | V | Without | |
| 5 Connection type | Code | C60, spring PFA coated | 7030 |
| Tube | | 11 Position of space saver-2 | Code |
| Flare connection with CPFA union nut | 73 | Without | |
| Flare connection with PVDF union nut | 75 | Space Saver for X+ Z position | S |
| Flare connection with PFA union nut | 77 | Space Saver for X position | X |
| 6 Valve body material | Code | Space Saver for Y position | Y |
| PFA, perfluoroalkoxy | 30 | Space Saver for Z position | Z |
| 7 Diaphragm material | Code | 12 Connection size 2 | Code |
| PTFE/EPDM one-piece | 54 | Position X and Z | |
| 8 Control function | Code | 1/2", international code-2: 8 | 8 |
| C60 / C60 | | 3/4", international code-2: 12 | 12 |
| Normally closed (NC) | 1 | 13 Connection type spigot 2 | Code |
| Normally open (NO) | 2 | Position X and Z | |
| Normally closed, normally open | D | Tube | |
| Normally open, normally closed | G | Flare connection with CPFA union nut | 73 |
| | | Flare connection with PVDF union nut | 75 |
| | | Flare connection with PFA union nut | 77 |
| 14 High Purity version | Code | 14 High Purity version | Code |
| High purity white | HPW | | |

Order example

| Ordering option | Code | Description |
|------------------------------|------|--|
| 1 Type | C60 | Diaphragm valve, pneumatically operated, plastic piston actuator, optical position indicator, stroke limiter (for actuator size 1–3 only) |
| 2 Position of space saver | Y | Space Saver for Y position |
| 3 Connection size | 8 | 1/2", international code: 8 |
| 4 Body configuration | V | Multi-port body V-form |
| 5 Connection type | 75 | Flare connection with PVDF union nut |
| 6 Valve body material | 30 | PFA, perfluoroalkoxy |
| 7 Diaphragm material | 54 | PTFE/EPDM one-piece |
| 8 Control function | F | Normally closed, manually operated |
| 9 Actuator version | 2 | Actuator size 2 |
| 10 Design | | Without |
| 11 Position of space saver-2 | S | Space Saver for X+ Z position |
| 12 Connection size 2 | 8 | 1/2", international code-2: 8 |
| 13 Connection type | 75 | Flare connection with PVDF union nut |
| 14 High Purity version | HPW | High purity white |

Technical data C67 PFA 3/5-way

Medium

Working medium: Corrosive, inert, gaseous and liquid media – in particular high-purity media – which have no negative impact on the physical and chemical properties of the body and diaphragm material.

Temperature

Media temperature: PFA valve body material (code 30): -10 – 150 °C

Observe pressure/temperature diagram

Ambient temperature: 0 – 60 °C


Storage temperature: 0 – 40 °C

Pressure

Operating pressure: 0 – 6 bar

Pressure/temperature diagram:

Valve body material PFA (code 30)



Note: The temperature/pressure diagram is only an aid. The data refers to water as a working medium. A change of operating conditions or other media may result in deviations. In case of doubt, it is advisable to test the behaviour of the material under the definitive operating conditions in a test installation. Temperatures below 0 °C can have a negative influence on the actuation speed.

Cv values:

| Actuator size | Body configuration | Connection size | Connection |
|---------------|--------------------|-----------------|------------|
| | | X, Y, Z | Tube |
| 2 | V | 1/2" | 28.0 |
| | | 3/4" | 53.0 |

Kv values in l/min

If the 2/2-way body has a tube and pipe connection, the Kv values of the tube connection are used.



Vacuum:

400 mbar absolute

The service life of the valve may be affected if exposed to a greater vacuum or when valves are installed on the pump suction side.

Pneumatic actuator**Control pressure:**

| Control function | Actuator size | Control pressure |
|------------------|---------------|------------------|
| 1 | 2 | 4 - 7 bar |
| 2, 3 | 2 | max. 4 bar |

Control pressure / operating pressure characteristics:**Control function 1 - normally closed (NC)****Control function 2 - normally open (NO)****Control air connection:**

G 1/8

Filling volume:

| Actuator size | Control function | | | |
|---------------|----------------------|--------------------|-----------------------------|---------------------------|
| | Normally closed (NC) | Normally open (NO) | Double acting (closed) (DA) | Double acting (open) (DA) |
| 2 | 24.0 | 39.0 | 39.0 | 24.0 |

Filling volume in cm³

Product conformities

Machinery Directive: 2006/42/EC


Food: FDA

EAC: The product is certified according to EAC.

Mechanical data

Flow direction: Optional

Dimensions C67 PFA 3/5-way



Dimensions in mm/inch

GEMÜ C67 CleanStar PVDF

Manually operated diaphragm valve with PVDF valve body



Features

- Ideal for high purity media (for example ultra pure water)
- High flow rate
- Minimal deadleg
- Optional flow direction
- Manufactured in cleanroom conditions
- Union end for easy radial installation and removal reduces maintenance costs

Description

Thanks to its PVDF body, the GEMÜ C67 CleanStar ultra pure 2/2-way diaphragm valve is ideally suited to ultra pure water applications. All media wetted parts are made of PVDF or PTFE (diaphragm). The external actuator parts are also made of PVDF. A seal adjuster and an optical position indicator are integrated as standard. The valve also has solid mounting lugs and a leakage sensor connection.

Technical specifications

- **Media temperature :** -10 to 120 °C
- **Ambient temperature:** 0 to 60 °C
- **Operating pressure :** 0 to 6 bar
- **Nominal size:** DN 15
- **Body configurations:** 2/2-way body
- **Connection types:** Union end
- **Connection standards:** DIN
- **Body materials:** PVDF
- **Diaphragm materials:** PTFE/EPDM
- **Conformities:** EAC | FDA | TA Luft (German Clean Air Act)

Technical data depends on the respective configuration

Availability C67 PVDF

| Actuator size | DN | Union end (code 7, 78) | Code |
|---------------|-----------|---------------------------|-----------|
| 2 | 15 | X | 15 |

Order data C67 PVDF

Order codes

The order data provide an overview of standard configurations.

Please check the availability before ordering. Other configurations available on request.

| | | | |
|--|-------------|------------------------------|-------------|
| 1 Type | Code | 5 Valve body material | Code |
| Diaphragm valve, manually operated, plastic handwheel, seal adjuster | C67 | PVDF | 20 |
| 2 DN | Code | 6 Diaphragm material | Code |
| DN 15 | 15 | PTFE/EPDM one-piece | 54 |
| 3 Body configuration | Code | 7 Control function | Code |
| 2/2-way body | D | Manually operated | 0 |
| 4 Connection type | Code | 8 Actuator version | Code |
| Union end with insert (socket) – DIN | 7 | Actuator size 2 | 2 |
| Union end with insert (for IR butt welding) – DIN | 78 | | |
| | | 9 High Purity version | Code |
| | | Without | |
| | | High Purity white | HPW |

Order example

| Ordering option | Code | Description |
|-----------------------|------|--|
| 1 Type | C67 | Diaphragm valve, manually operated, plastic handwheel, seal adjuster |
| 2 DN | 15 | DN 15 |
| 3 Body configuration | D | 2/2-way body |
| 4 Connection type | 78 | Union end with insert (for IR butt welding) – DIN |
| 5 Valve body material | 20 | PVDF |
| 6 Diaphragm material | 54 | PTFE/EPDM one-piece |
| 7 Control function | 0 | Manually operated |
| 8 Actuator version | 2 | Actuator size 2 |
| 9 High Purity version | HPW | High Purity white |

Technical data C67 PVDF

Medium

Working medium: Corrosive, inert, gaseous and liquid media – in particular high-purity media – which have no negative impact on the physical and chemical properties of the body and diaphragm material.

Temperature

Media temperature: Valve body material PVDF (code 20): -10 – 120 °C
Observe pressure/temperature diagram


Ambient temperature: 0 – 60 °C

Storage temperature: 0 – 40 °C

Pressure

Operating pressure: 0 – 6 bar

Pressure/temperature diagram: Valve body material PVDF (code 20)



Note: The temperature/pressure diagram is only an aid. The data refers to water as a working medium. A change of operating conditions or other media may result in deviations. In case of doubt, it is advisable to test the behaviour of the material under the definitive operating conditions in a test installation. Temperatures below 0 °C can have a negative influence on the actuation speed.

Cv values:

| Actuator size | DN | Connection size | | Connection |
|---------------|----|-----------------|-----------|------------|
| | | Pipe | Union end | |
| 2 | 15 | 1/2" | 68.0 | |

Kv values in l/min

Vacuum:

400 mbar absolute

The service life of the valve may be affected if exposed to a greater vacuum or when valves are installed on the pump suction side.

Product conformities

Machinery Directive: 2006/42/EC

Food: FDA


EAC: The product is certified according to EAC.

Mechanical data

Flow direction: Optional

Dimensions C67 PVDF

Union end (code 7, 78)




| Actuator size | DN | B | H | L | L1 | L2 |
|---------------|----|------|-------|---|---------------------------|----|
| 2 | 15 | 57.0 | 114.0 | | see connection dimensions | |

Dimensions in mm


Connection dimensions

Union end (code 7)



Dimensions in mm


Union end (code 78)



Dimensions in mm

Mounting dimensions

2/2-way valve (code D)




2/2-way valves (code D)

| Actuator size | $\varnothing d$ | A | B | C |
|------------------------|-----------------|------|------|------|
| 2, 2E, 2 F, 2EF | 5.5 | 61.5 | 31.0 | 40.0 |

Dimensions in mm

Mounting holes, round and slotted hole



Dimensions in mm

Dear customers,

In order to simplify installation, we are switching over the mounting holes to slotted holes for all valve sizes.

Due to the gradual changeover in manufacturing, you may therefore receive valve bodies with new slotted holes and also with the old, round boreholes during this phase.

We ask for your understanding in this matter.

GEMÜ C67 CleanStar SmartLine

Manually operated SmartLine diaphragm valve with PP valve body



Features

- Improved flow capability over PFA versions
- Affordable CleanStar type for applications with less strict requirements in terms of purity
- PTFE diaphragm
- Choice of valve bodies made of PP-R natural or PP-H grey
- Manufactured in a monitored atmosphere

Description

The GEMÜ C67 HPW CleanStar ultra pure 2/2-way diaphragm valve is manually operated. All media wetted parts are made of PP or PTFE (diaphragm). The external actuator parts are made of PVDF. This GEMÜ C67 HPW CleanStar 2/2-way diaphragm valve has a valve body made of PP and is therefore an affordable alternative to the ultra pure designs. It has been specifically developed for industrial applications with less strict purity requirements (for example solar energy industry). A seal adjuster and an optical position indicator are integrated as standard. A leakage sensor connection is provided.

Technical specifications

- **Media temperature :** -10 to 80 °C
- **Ambient temperature:** 0 to 60 °C
- **Operating pressure :** 0 to 6 bar
- **Nominal sizes:** DN 10 to 32
- **Body configurations:** 2/2-way body
- **Connection types:** Butt weld spigot | Flare | Union end
- **Connection standards:** DIN
- **Body materials:** PP-H, grey | PP-H, natural
- **Diaphragm materials:** PTFE/EPDM
- **Conformities:** EAC | FDA | TA Luft (German Clean Air Act)

Technical data depends on the respective configuration

Availability C67 SmartLine

| Actuator size | DN | Flare connection | Butt weld spigot | | Union end | Code |
|---------------|-----------|------------------|----------------------|-------------------|-----------|-----------|
| | | | Connection size X, Z | Connection size Z | | |
| 2 | 10 | 1/2" - 1/2" | - | On request | - | 8 |
| | 15 | - | 15 - 15 | On request | - | 15 |
| | 15 | 3/4" - 3/4" | - | On request | - | 12 |
| | 20 | - | 20 - 20 | On request | - | 20 |
| | 20 | 1" - 1" | - | On request | - | 16 |
| | 25 | - | 25 - 25 | On request | - | 25 |
| 3 | 20 | - | 20 - 20 | On request | - | 20 |
| | 25 | 1" - 1" | - | On request | - | 16 |
| | 25 | - | 25 - 25 | On request | - | 25 |
| | 25 | - | - | On request | 25 - 25 | 25 |
| | 25 | 1 1/4" - 1 1/4" | - | On request | - | 20 |
| | 32 | - | 32 - 32 | On request | - | 32 |

Order data C67 SmartLine

Order codes

The order data provide an overview of standard configurations.

Please check the availability before ordering. Other configurations available on request.

| 1 Type | Code | 4 Connection type | Code |
|--|------|---|------|
| Diaphragm valve, manually operated, plastic handwheel, seal adjuster | C67 | Flare connection with PFA union nut | 77 |
| Union end with DIN insert (for IR butt welding) | | Union end with DIN insert (for IR butt welding) | 78 |
| 2 Connection size | Code | 5 Valve body material | Code |
| 1/2", international code: 8 | 8 | PP-H, grey | G5 |
| DN 15 | 15 | PP-R, natural | R5 |
| 3/4", international code: 12 | 12 | | |
| DN 20 | 20 | | |
| 1", international code: 16 | 16 | | |
| DN 25 | 25 | | |
| 1 1/4", international code: 20 | 20 | | |
| DN 32 | 32 | | |
| 3 Body configuration | Code | 6 Diaphragm material | Code |
| 2/2-way body | D | PTFE/EPDM one-piece | 54 |
| 4 Connection type | Code | 7 Control function | Code |
| Spigot for IR butt welding | 20 | Manually operated | 0 |
| Flare connection with PVDF union nut | 75 | | |
| 8 Actuator version | Code | 9 High Purity version | Code |
| | | Without | |
| | | Smart Line | HPS |

Order example

| Ordering option | Code | Description |
|-----------------------|------|--|
| 1 Type | C67 | Diaphragm valve, manually operated, plastic handwheel, seal adjuster |
| 2 Connection size | 8 | 1/2", international code: 8 |
| 3 Body configuration | D | 2/2-way body |
| 4 Connection type | 78 | Union end with DIN insert (for IR butt welding) |
| 5 Valve body material | G5 | PP-H, grey |
| 6 Diaphragm material | 54 | PTFE/EPDM one-piece |
| 7 Control function | 0 | Manually operated |
| 8 Actuator version | 2 | Actuator size 2 |
| 9 High Purity version | HPS | Smart Line |

Technical data C67 SmartLine

Medium

Working medium: Corrosive, inert, gaseous and liquid media – in particular high-purity media – which have no negative impact on the physical and chemical properties of the body and diaphragm material.

Temperature

Media temperature: Valve body material PP-H (code G5, R5): -10 – 80 °C
Observe pressure/temperature diagram


Ambient temperature: 0 – 60 °C

Storage temperature: 0 – 40 °C

Pressure

Operating pressure: 0 – 6 bar

Pressure/temperature diagram:



Note: The temperature/pressure diagram is only an aid. The data refers to water as a working medium. A change of operating conditions or other media may result in deviations. In case of doubt, it is advisable to test the behaviour of the material under the definitive operating conditions in a test installation. Temperatures below 0 °C can have a negative influence on the actuation speed.

Cv values:

| Actuator size | Connection size | DN | Connection type | Connection | | |
|---------------|-----------------|----|-----------------|------------|-------|------|
| | | | | Code | Tube | Pipe |
| 2 | 1/2" | 10 | 75, 77 | 34.2 | - | |
| | | 15 | 20 | - | 82.5 | |
| | 3/4" | 15 | 75 | 86.7 | - | |
| | | 20 | 20 | - | 83.7 | |
| | 20 | 20 | - | | 171.7 | |
| | 1" | 20 | 75, 77 | 93.3 | - | |
| | | 25 | 20 | - | 94.0 | |
| | | 20 | 75, 77 | 183.3 | - | |
| | | 25 | 20 | - | 233.3 | |
| | | 25 | 78 | - | 233.3 | |
| | 1 1/4" | 25 | 75, 77 | 238.3 | - | |
| | | 32 | 20 | - | 238.3 | |

Kv values in l/min

Vacuum: 400 mbar absolute

The service life of the valve may be affected if exposed to a greater vacuum or when valves are installed on the pump suction side.

Product conformities

Machinery Directive: 2006/42/EC

Food: FDA


EAC: The product is certified according to EAC.

Mechanical data

Flow direction: Optional

Dimensions C67 SmartLine


Flare connection (code 75, 77)



| Actuator size | Connection size | ØB | ØB1 | H | H1 | L | L1 | L2 |
|---------------|-----------------|------|------|-------|------|-------|------|------|
| 2 | 1/2" | 64.0 | 60.0 | 120.5 | 16.0 | 131.8 | 65.9 | 65.9 |
| | 3/4" | 64.0 | 60.0 | 124.5 | 19.0 | 133.8 | 66.9 | 66.9 |
| | 1" | 64.0 | 60.0 | 124.5 | 25.0 | 160.0 | 80.0 | 80.0 |
| 3 | 1" | 80.0 | 90.0 | 160.5 | 25.0 | 180.0 | 90.0 | 90.0 |
| | 1 1/4" | 80.0 | 90.0 | 160.5 | 25.0 | 192.0 | 96.0 | 96.0 |

Dimensions in mm


Butt weld spigot (code 20)



| Actuator size | Connec-tion size | $\varnothing B$ | $\varnothing B1$ | H | $H1$ | L | $L1$ | $L2$ | Spigot (A) | |
|---------------|------------------|-----------------|------------------|-------|------|-------|------|------|-----------------|------------------|
| | | | | | | | | | $\varnothing d$ | $\varnothing d1$ |
| 2 | 15 | 64.0 | 60.0 | 124.5 | 19.0 | 131.0 | 65.5 | 65.5 | 20.0 | 16.2 |
| | 20 | 64.0 | 60.0 | 124.5 | 19.0 | 131.0 | 65.5 | 65.5 | 25.0 | 20.4 |
| | 25 | 64.0 | 60.0 | 124.5 | 19.0 | 145.0 | 72.5 | 42.5 | 32.0 | 26.0 |
| 3 | 20 | 80.0 | 90.0 | 160.5 | 25.0 | 166.0 | 83.0 | 83.0 | 25.0 | 20.4 |
| | 25 | 80.0 | 90.0 | 160.5 | 25.0 | 166.0 | 83.0 | 83.0 | 32.0 | 26.0 |
| | 32 | 80.0 | 90.0 | 160.5 | 25.0 | 172.0 | 86.0 | 86.0 | 40.0 | 32.6 |

Dimensions in mm


Union end (code 78)



Dimensions in mm/inch

Mounting dimensions

2/2-way valve (code D)




2/2-way valves (code D)

| Actuator size | $\varnothing d$ | A | B | C |
|-----------------|-----------------|------|------|------|
| 2, 2E, 2 F, 2EF | 5.5 | 61.5 | 31.0 | 40.0 |
| 3, 3E, 3 F, 3EF | 6.5 | 78.0 | 39.0 | 56.0 |

Dimensions in mm

Mounting holes, round and slotted hole



Dimensions in mm

Dear customers,

In order to simplify installation, we are switching over the mounting holes to slotted holes for all valve sizes.

Due to the gradual changeover in manufacturing, you may therefore receive valve bodies with new slotted holes and also with the old, round boreholes during this phase.

We ask for your understanding in this matter.

Accessories



GEMÜ CFSTF

Service tool for flare union nuts

The GEMÜ CFSTF service tool is used for the assembly of GEMÜ CF flare union nuts in PFA, PVDF and carbon fibre reinforced PFA. A precisely defined torque can be achieved when using it in combination with a torque wrench.



GEMÜ 1098

Flaring mandrel

The GEMÜ 1098 flaring mandrel is an assembly tool for flare connections.



GEMÜ FlareStar

PFA fittings

Over 1,000 different types of fitting are produced under cleanroom conditions in compliance with DIN 16901-140. The fitting bodies are made of PFA, while the union nuts are made of PFA, PVDF or CPFA. We can also supply all standard market connections.



GEMÜ TubeStar

Tube

TubeStar is a product range comprising ultra-pure and standard PFA tubing. The tubes are particularly suitable for applications with high-purity media and other chemicals.



GEMÜ C67 STA

Service tool for actuators

Service tool for installation and removal of the central union nut.



GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG
Fritz-Müller-Straße 6-8, 74653 Ingelfingen-Criesbach, Germany
Phone +49 (0) 7940 1230 · info@gemue.de
www.gemu-group.com