

GEMÜ 639 eSyStep

Motorized diaphragm valve



Features

- CIP/SIP capable
- Open/close function or with integrated positioner
- Actuating speed max. 3 mm/s
- Parameterizable via IO-Link
- On-site or remote end position programming via programming input
- Various functions integrated (e.g. feedback, stroke limiter, etc.)

Description

The GEMÜ 639 eSyStep is an electrically operated 2/2-way diaphragm valve. The eSyStep electric actuator is available as On/Off actuator or with integrated positioner. An integral optical and electrical position indicator is standard. The self-locking actuator holds its position in a stable manner when idle and in the event of power supply failure.

Technical specifications

- **Media temperature:** 14 to 212 °F
- **Sterilization temperature:** max. 302 °F
- **Ambient temperature:** 32 to 140 °F
- **Operating pressure:** 0 to 150 psi
- **Nominal sizes:** - (DN 4) to 1 1/2" (DN 40)
- **Body configurations:** 2/2-way body | i-body | Multi-port body | Tank valve body | T-body | Welding configuration
- **Connection standards:** ANSI | ASME | BS | DIN | EN | ISO | JIS | SMS
- **Body materials:** 1.4408, investment casting material | 1.4408, investment casting material, PFA lined | 1.4435 (316L), forged material | 1.4435 (BN2), forged material | 1.4435, investment casting material | 1.4539 (904L), forged material | CW614N, brass | CW617N, brass | EN-GJS-400-18-LT, SG iron material | EN-GJS-400-18-LT, SG iron material with hard rubber lining | EN-GJS-400-18-LT, SG iron material, PFA lined | EN-GJS-400-18-LT, SG iron material, PP lined
- **Body lining:** Hard rubber | PFA | PP
- **Diaphragm materials:** CR | EPDM | FKM | NBR | PTFE/EPDM
- **Supply voltage:** 24 V DC
- **Actuating speed:** max. 3 mm/s
- **Protection class:** IP 65
- **Conformities:** Belgaqua | BSE/TSE | EAC | EHEDG | FDA | Oxygen | Reg. (EU) No. 10/2011 | Regulation (EC) No. 1935/2004 | Regulation (EC) No. 2023/2006 | TA Luft (German Clean Air Act) | USP

Technical data depends on the respective configuration




further information
webcode: GW-639



Product description

Construction



Item	Name	Materials
1	Optical position indicator	PA 12
2	Manual override	
3	Actuator top with LED display	Reinforced polyamide
4	Actuator base	Reinforced polyamide
5	Valve body	EN-GJS-400-18-LT (GGG 40.3) EN-GJS-400-18-LT (GGG 40.3), PFA lined EN-GJS-400-18-LT (GGG 40.3), PP lined EN-GJS-400-18-LT (GGG 40.3), hard rubber lined 1.4408, investment casting 1.4408, PFA lined 1.4435 (F316L), forged body 1.4435 (BN2), forged body, $\Delta Fe < 0.5 \%$ 1.4435, investment casting 1.4539, forged body CW614N, CW617N (brass)
6	Diaphragm	CR, EPDM, FKM, NBR, PTFE/EPDM (one-piece), PTFE/EPDM (two-piece)
7	CONEXO diaphragm RFID chip (see Conexo information)	
8	CONEXO body RFID chip (see Conexo information)	
9	Electrical connections	
10	CONEXO actuator RFID chip (see Conexo information)	

GEMÜ CONEXO

The interaction of valve components that are equipped with RFID chips and an associated IT infrastructure actively increase process reliability.



Thanks to serialization, every valve and every relevant valve component such as the body, actuator or diaphragm, and even automation components, can be clearly traced and read using the CONEXO pen RFID reader. The CONEXO app, which can be installed on mobile devices, not only facilitates and improves the "installation qualification" process, but also makes the maintenance process much more transparent and easier to document. The app actively guides the maintenance technician through the maintenance schedule and directly provides him with all the information assigned to the valve, such as test reports, testing documentation and maintenance histories. The CONEXO portal acts as a central element, helping to collect, manage and process all data.

For further information on GEMÜ CONEXO please visit:

www.gemu-group.com/conexo

Ordering

GEMÜ Conexo must be ordered separately with the ordering option "CONEXO".

Overview of available functions

Function	Control module – OPEN/CLOSE control (Code AE, A5, A6)	Control module – positioner (Code S0, S5, S6)
OPEN/CLOSE control	X	X
Positioner		X
Manual override	X	X
Optical status and position indicator	X	X
On-site initialization	X	X
Deactivation of on-site initialization	X	X
Initialization via digital input	X	X
Initialization via IO-Link	X	X
Feedback for operating mode	X	X
Actuation OPEN	X	X
Actuation CLOSED	X	X
Actuation, analogue		X
Position feedback OPEN	X	X
Position feedback CLOSED	X	X
Position feedback analogue		X
Location function	X	X
Error output	X	X
Actuating speed adjustable	X	
Actuating force adjustable	X	X
Inversion of LED colours	X	X
Cycle counter	X	
Error counter	X	
Operating time determination	X	X
Switch point setting (tolerance)	X	X
Inversion input/output logic	X	X
Adjustable error action	X	X
Safe/On	X	X
Direction reversal		X
Open tight		X
Close tight		X
Split range		X
Stroke limiter/seal adjuster		X

Availability

Availability of grades of surface finish

Internal surface finishes for forged and block material bodies ¹⁾

Readings for Process Contact Surfaces	Mechanically polished ²⁾		Electropolished	
	Hygienic class DIN 11866	Code	Hygienic class DIN 11866	Code
Ra ≤ 0.80 µm	H3	1502	HE3	1503
Ra ≤ 0.60 µm	-	1507	-	1508
Ra ≤ 0.40 µm	H4	1536	HE4	1537
Ra ≤ 0.25 µm ³⁾	H5	1527	HE5	1516

Readings for Process Contact Surfaces acc. to ASME BPE 2016 ⁴⁾	Mechanically polished ²⁾		Electropolished	
	ASME BPE Surface Designation	Code	ASME BPE Surface Designation	Code
Ra Max. = 0.76 µm (30 µinch)	SF3	SF3	-	-
Ra Max. = 0.64 µm (25 µinch)	SF2	SF2	SF6	SF6
Ra Max. = 0.51 µm (20 µinch)	SF1	SF1	SF5	SF5
Ra Max. = 0.38 µm (15 µinch)	-	-	SF4	SF4

Internal surface finishes for investment cast bodies

Readings for Process Contact Surfaces	Mechanically polished ²⁾	
	Hygienic class DIN 11866	Code
Ra ≤ 6.30 µm	-	1500
Ra ≤ 0.80 µm	H3	1502
Ra ≤ 0.60 µm	-	1507

Ra acc. to DIN EN ISO 4288 and ASME B46.1

- 1) Surface finishes of customized valve bodies may be limited in special cases.
- 2) Or any other finishing method that meets the Ra value (acc. to ASME BPE).
- 3) The maximum Ra finish achievable for pipe connections with an internal pipe diameter < 6 mm is 0.38 µm.
- 4) When using these surfaces, the bodies are marked according to the specifications of ASME BPE.
The surfaces are only available for valve bodies which are made of materials (e.g. GEMÜ material codes 40, 41, F4, 44)) and use connections (e.g. GEMÜ connection codes 59, 80, 88) according to ASME BPE.

See also

- ▣ Availability of grades of surface finish [▶ 5]

Availability of valve bodies

Spigot

M G	DN	Connection type code ¹⁾																
		0		16	17	18	35	36	37		55	59	60		63	64	65	
		Material code ²⁾																
		C3	40, 42, F4	40, 42, F4	C3, 40, 42, F4	40, 42, F4	40, 42, F4	40, 42, F4	C3	40, 42, F4	40, 42, F4	C3	40, 42, F4	C3	40, 42, F4	40, 42, F4	40, 42, F4	40, 42, F4
8	4	X	X	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	6	-	-	-	X	-	-	X	-	-	-	-	-	-	X	X	-	X
	8	-	-	-	X	-	-	X	-	-	X	X	X	X	X	X	-	X
	10	-	-	X	X	X	-	-	-	-	X	X	X	-	-	-	-	-
	15	-	-	-	-	-	-	-	-	-	X	X	X	-	-	-	-	-
10	10	-	-	X	X	X	-	X	-	-	X	-	X	X	X	X	-	X
	15	-	X	X	X	X	-	X	-	-	X	-	X	X	X	X	X	X
	20	-	-	-	-	-	-	-	-	-	X	X	X	-	-	-	-	-
25	15	-	X	X	X	X	-	X	-	-	-	-	-	X	X	X	X	X
	20	-	X	X	X	X	-	X	-	-	X	X	X	X	X	X	X	X
	25	-	X	X	X	X	X	X	X	X	-	X	X	X	X	X	X	X
40	32	-	X	X	X	X	X	X	-	X	-	-	-	X	X	X	X	X
	40	-	X	X	X	X	X	X	X	X	-	X	X	X	X	X	X	X

MG = diaphragm size, X = standard

1) Connection type

Code 0: Spigot DIN

Code 16: Spigot DIN EN 10357 series B (2014 edition; formerly DIN 11850 series 1)

Code 17: Spigot EN 10357 series A/DIN 11866 series A formerly DIN 11850 series 2

Code 18: Spigot DIN 11850 series 3

Code 35: Spigot JIS-G 3447

Code 36: Spigot JIS-G 3459 schedule 10s

Code 37: Spigot SMS 3008

Code 55: Spigot BS 4825, part 1

Code 59: Spigot ASME BPE / DIN 11866 series C

Code 60: Spigot ISO 1127/DIN EN 10357 series C (2014 edition)/DIN 11866 series B

Code 63: Spigot ANSI/ASME B36.19M Schedule 10s

Code 64: Spigot ANSI/ASME B36.19M schedule 5s

Code 65: Spigot ANSI/ASME B36.19M Schedule 40s

2) Valve body material

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code C3: 1.4435, investment casting

Code F4: 1.4539, forged body

Threaded connection

MG	DN	Connection type code ¹⁾				
		1			31	6, 6K
		Material code ²⁾				
		12	37	90	37, 90	40, 42
8	8	-	X	-	-	-
	10	-	-	-	-	W
10	10	-	-	-	-	W
	12	X	X	-	-	-
	15	X	X	-	-	W
25	15	-	X	X	X	W
	20	-	X	X	X	W
	25	-	X	X	X	W
40	32	-	X	X	X	W
	40	-	X	X	X	W

MG = diaphragm size, X = standard

W = welded assembly

1) **Connection type**

Code 1: Threaded socket DIN ISO 228

Code 31: NPT female thread

Code 6: Threaded spigot DIN 11851

Code 6K: Cone spigot and union nut DIN 11851

2) **Valve body material**

Code 12: CW614N, CW617N (brass)

Code 37: 1.4408, investment casting

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code 90: EN-GJS-400-18-LT (GGG 40.3)

Flange

MG	DN	Connection type code ¹⁾					
		8		34	38	39	
		Material code ²⁾					
		17, 18, 39, 83, 90	40, 42, C3	39	17, 18 ³⁾ , 39, 83	17, 18, 39, 83, 90	40, 42, C3
25	15	X	W	X	-	X	W
	20	X	W	X	X	X	W
	25	X	W	X	X	X	W
40	32	X	W	X	-	X	W
	40	X	W	X	X	X	W

MG = diaphragm size, X = standard

W = welded assembly

1) **Connection type**

Code 8: Flange EN 1092, PN 16, form B, face-to-face dimension FTF EN 558 series 1, ISO 5752, basic series 1, length only for body configuration D

Code 34: Flange JIS B2220, 10K, RF, face-to-face dimension FTF EN 558 series 1, ISO 5752, basic series 1, length only for body configuration D

Code 38: Flange ANSI Class 150 RF, length only for body configuration D acc. to MSS SP-88

Code 39: Flange ANSI Class 125/150 RF, length only for body configuration D acc. to EN 558 series 1, ISO 5752, basic series 1

2) **Valve body material**

Code 17: EN-GJS-400-18-LT (GGG 40.3), PFA lined

Code 18: EN-GJS-400-18-LT (GGG 40.3), PP lined

Code 39: 1.4408, PFA lined

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code 83: EN-GJS-400-18-LT (GGG 40.3), hard rubber lined

Code 90: EN-GJS-400-18-LT (GGG 40.3)

Code C3: 1.4435, investment casting

3) On request

Clamp

MG	DN	Connection type code ¹⁾						
		80	82	88	8A	8E	8P	8T
		Material code ²⁾						
		40, 42, F4	40, 42, F4	40, 42, F4	40, 42, F4	40, 42, F4	40, 42, F4	40, 42, F4
8	6	-	K	-	K	-	-	-
	8	K	K	-	K	-	K	-
	10	K	-	-	W	-	K	-
	15	K	-	W	-	-	K	W
10	10	-	K	-	K	-	-	-
	15	K	W	K	K	-	K	K
	20	K	-	K	-	-	K	K
25	15	-	W	-	K	-	-	-
	20	K	K	K	K	-	K	K
	25	K	K	K	K	K	K	K
40	32	-	W	-	K	K	-	-
	40	K	W	K	K	K	K	K

MG = diaphragm size

K = connections completely machined (not welded)

W = welded assembly

1) Connection type

Code 80: Clamp ASME BPE, length only for body configuration D acc. to ASME BPE

Code 82: Clamp DIN 32676 series B, face-to-face dimension FTF EN 558 series 7, length only for body configuration D

Code 88: Clamp ASME BPE, for pipe ASME BPE, face-to-face dimension FTF EN 558 series 7, length only for body configuration D

Code 8A: Clamp DIN 32676 series A, face-to-face dimension FTF acc. to EN 558 series 7, length only for body configuration D

Code 8E: Clamp ISO 2852 for pipe ISO 2037, clamp SMS 3017 for pipe SMS 3008 face-to-face dimension FTF EN 558 series 7, length only for body configuration D

2) Valve body material

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code F4: 1.4539, forged body

Availability of product compliance

	Diaphragm material code ¹⁾	Body material code ²⁾
Drinking water		
Belgaqua (B)	28	37

1) Diaphragm material

Code 28: EPDM

2) Valve body material

Code 37: 1.4408, investment casting

Order data

The order data provide an overview of standard configurations.

Please check the availability before ordering. Other configurations available on request.

Order codes

1 Type	Code
Diaphragm valve, electrically operated, eSyStep	639

2 DN	Code
DN 4	4
DN 6	6
DN 8	8
DN 10	10
DN 12	12
DN 15	15
DN 20	20
DN 25	25
DN 32	32
DN 40	40

3 Body configuration	Code
Tank bottom valve body	B
Without	
2/2-way body	D
T body	T
Without	

4 Connection type	Code
Spigot	
Spigot DIN	0
Spigot DIN EN 10357 series B (2014 edition; formerly DIN 11850 series 1)	16
Spigot EN 10357 series A/DIN 11866 series A formerly DIN 11850 series 2	17
Spigot DIN 11850 series 3	18
Spigot JIS-G 3447	35
Spigot JIS-G 3459 schedule 10s	36
Spigot SMS 3008	37
Spigot BS 4825, part 1	55
Spigot ASME BPE / DIN 11866 series C	59
Spigot ISO 1127/DIN EN 10357 series C (2014 edition)/DIN 11866 series B	60
Spigot ANSI/ASME B36.19M Schedule 10s	63
Spigot ANSI/ASME B36.19M schedule 5s	64
Spigot ANSI/ASME B36.19M Schedule 40s	65
Threaded socket DIN ISO 228	1
NPT female thread	31
Threaded spigot DIN 11851	6
Cone spigot and union nut DIN 11851	6K

4 Connection type	Code
Flange	
Flange EN 1092, PN 16, form B, face-to-face dimension FTF EN 558 series 1, ISO 5752, basic series 1, length only for body configuration D	8
Flange JIS B2220, 10K, RF, face-to-face dimension FTF EN 558 series 1, ISO 5752, basic series 1, length only for body configuration D	34
Flange ANSI Class 150 RF, length only for body configuration D acc. to MSS SP-88	38
Flange ANSI Class 125/150 RF, length only for body configuration D acc. to EN 558 series 1, ISO 5752, basic series 1	39
Clamp	
Clamp ASME BPE, length only for body configuration D acc. to ASME BPE	80
Clamp DIN 32676 series B, face-to-face dimension FTF EN 558 series 7, length only for body configuration D	82
Clamp ASME BPE, for pipe ASME BPE, face-to-face dimension FTF EN 558 series 7, length only for body configuration D	88
Clamp DIN 32676 series A, face-to-face dimension FTF acc. to EN 558 series 7, length only for body configuration D	8A
Clamp ISO 2852 for pipe ISO 2037, clamp SMS 3017 for pipe SMS 3008 face-to-face dimension FTF EN 558 series 7, length only for body configuration D	8E
Clamp DIN 32676 series C, face-to-face dimension FTF ASME BPE, length only for body configuration D	8P
Clamp DIN 32676 series C, face-to-face dimension FTF EN 558 series 7, length only for body configuration D	8T

5 Valve body material	Code
SG iron material	
EN-GJS-400-18-LT (GGG 40.3), PFA lined	17
EN-GJS-400-18-LT (GGG 40.3), PP lined	18
EN-GJS-400-18-LT (GGG 40.3), hard rubber lined	83
EN-GJS-400-18-LT (GGG 40.3)	90
Investment casting material	
1.4408, investment casting	37
1.4408, PFA lined	39
1.4435, investment casting	C3

5 Valve body material	Code
Forged material	
1.4435 (F316L), forged body	40
1.4435 (BN2), forged body, Fe < 0.5%	42
1.4539, forged body	F4
Brass	
CW614N, CW617N (brass)	12

6 Diaphragm material	Code
Elastomer	
NBR	2
EPDM	3A
FKM	4
FKM	4A
CR	8
EPDM	13
EPDM	17
EPDM	19
EPDM	28
EPDM	29
PTFE	
PTFE/EPDM one-piece	54
PTFE/EPDM two-piece	5M
Note: The PTFE/EPDM diaphragm (code 5M) is available from diaphragm size 25.	

7 Voltage/Frequency	Code
24 V DC	C1

8 Control module	Code
ON/OFF actuator, additional end position indicators	AE
ON/OFF actuator, additional end position indicators, configured for emergency power supply module (NC)	A5
ON/OFF actuator, additional end position indicators, configured for emergency power supply module (NO)	A6
Positioner	S0
Positioner, configured for emergency power supply module (NC)	S5
Positioner, configured for emergency power supply module (NO)	S6

9 Surface	Code
Ra ≤ 6.3 μm (250 μin.) for media wetted surfaces, mechanically polished internal	1500
Ra ≤ 0.8 μm (30 μin.) for media wetted surfaces, in accordance with DIN 11866 H3, mechanically polished internal	1502
Ra ≤ 0.8 μm (30 μin.) for media wetted surfaces, in accordance with DIN 11866 HE3, electropolished internal/external	1503
Ra ≤ 0.6 μm (25 μin.) for media wetted surfaces, mechanically polished internal	1507
Ra ≤ 0.6 μm (25 μin.) for media wetted surfaces, electropolished internal / external	1508
Ra ≤ 0.4 μm (15 μin.) for media wetted surfaces, in accordance with DIN 11866 H4, mechanically polished internal	1536

9 Surface	Code
Ra ≤ 0.4 μm (15 μin.) for media wetted surfaces, in accordance with DIN 11866 HE4, electropolished internal / external	1537
Ra ≤ 0.25 μm (10 μin.) for media wetted surfaces *), in accordance with DIN 11866 HE5, electropolished internal/external, *) for inner pipe diameter < 6 mm, in spigots Ra ≤ 0.38 μm	1516
Ra ≤ 0.25 μm (10 μin.) for media wetted surfaces *), in accordance with DIN 11866 H5, mechanically polished internal, *) for inner pipe diameter < 6 mm, in spigots Ra ≤ 0.38 μm	1527
Ra max. 0.51 μm (20 μin.) for media wetted surfaces, in accordance with ASME BPE SF1, mechanically polished internal	SF1
Ra max. 0.64 μm (25 μin.) for media wetted surfaces, in accordance with ASME BPE SF2, mechanically polished internal	SF2
Ra max. 0.76 μm (30 μin.) for media wetted surfaces, in accordance with ASME BPE SF3, mechanically polished internal	SF3
Ra max. 0.38 μm (15 μin.) for media wetted surfaces, in accordance with ASME BPE SF4, electropolished internal/external	SF4
Ra max. 0.51 μm (20 μin.) for media wetted surfaces, in accordance with ASME BPE SF5, electropolished internal/external	SF5
Ra max. 0.64 μm (25 μin.) for media wetted surfaces, in accordance with ASME BPE SF6, electropolished internal/external	SF6

10 Actuator version	Code
DN 4 - 15, diaphragm size 8	
Actuator size 0 diaphragm size 8	0B
DN 10-20, diaphragm size 10	
Actuator size 0	0A
DN 15 - 25, diaphragm size 25	
Actuator size 1	1A
DN 32 - 40, diaphragm size 40	
Actuator size 1	1A

11 Special version	Code
Without	
BELGAQUA certification	B
Special version for oxygen, maximum medium temperature: 60° C	S

12 CONEXO	Code
Without	
Integrated RFID chip for electronic identification and traceability	C

Order example

Order option	Code	Description
1 Type	639	Diaphragm valve, electrically operated, eSyStep
2 DN	15	DN 15
3 Body configuration	D	2/2-way body
4 Connection type	60	Spigot ISO 1127/DIN EN 10357 series C (2014 edition)/DIN 11866 series B
5 Valve body material	40	1.4435 (F316L), forged body
6 Diaphragm material	54	PTFE/EPDM one-piece
7 Voltage/Frequency	C1	24 V DC
8 Control module	S0	Positioner
9 Surface	1503	Ra ≤ 0.8 µm (30 µin.) for media wetted surfaces, in accordance with DIN 11866 HE3, electropolished internal/external
10 Actuator version	0A	Actuator size 0
11 Special version		Without
12 CONEXO	C	Integrated RFID chip for electronic identification and traceability

Technical data

Medium

Working medium: Corrosive, inert, gaseous and liquid media which have no negative impact on the physical and chemical properties of the body and diaphragm material.
 Special version for oxygen (code S): only gaseous oxygen


Temperature

Media temperature:

Diaphragm material	Standard	Special version for oxygen
NBR (code 2)	14 – 212 °F	-
FKM (code 4)	14 – 194 °F	-
CR (code 8)	14 – 212 °F	-
EPDM (code 13)	14 – 212 °F	32 – 140 °F
EPDM (code 17)	14 – 212 °F	-
EPDM (code 19)	14 – 212 °F	32 – 140 °F
EPDM (code 28)	-10 – 85 °F	-
EPDM (code 29)	14 – 212 °F	-
PTFE/EPDM (code 54)	14 – 212 °F	32 – 140 °F
PTFE/EPDM (code 5M)	14 – 212 °F	32 – 140 °F

Sterilisation temperature: EPDM (code 13) max. 302 °F, max. 60 min per cycle
 EPDM (code 17) max. 302 °F, max. 180 min per cycle
 EPDM (code 19) max. 302 °F, max. 180 min per cycle
 PTFE/EPDM (code 54) max. 302 °F, permanent temperature per cycle
 PTFE/EPDM (code 5M) max. 302 °F, permanent temperature per cycle

The sterilisation temperature is only valid for steam (saturated steam) or superheated water. If the sterilisation temperatures listed above are applied to the EPDM diaphragms for longer periods of time, the service life of the diaphragms will be reduced. In these cases, maintenance cycles must be adapted accordingly. PTFE diaphragms can also be used as moisture barriers; however, this will reduce their service life. This also applies to PTFE diaphragms exposed to high temperature fluctuations. The maintenance cycles must be adapted accordingly. GEMÜ 555 and 505 globe valves are particularly suitable for use in the area of steam generation and distribution. The following valve arrangement for interfaces between steam pipes and process pipes has proven itself over time: A globe valve for shutting off steam pipes and a diaphragm valve as an interface to the process pipes.



Ambient temperature: 32 – 140 °F

Storage temperature: 32 – 104 °F

Pressure

Operating pressure:

MG	DN	Actuator version	Diaphragm material		
			Elastomer	PTFE	
				Forged material	Cast material with and without lining
8	4 - 15	0B	0 - 145	0 - 145	0 - 87
10	10 - 20	0A	0 - 145	0 - 145	0 - 87
25	15 - 25	1A	0 - 120	0 - 120	0 - 87
40	32 - 40	1A	0 - 120	0 - 58	0 - 58

MG = diaphragm size

All pressures are gauge pressures. Operating pressure values were determined with static operating pressure applied on one side of a closed valve. Sealing at the valve seat and atmospheric sealing is ensured for the given values.

Information on operating pressures applied on both sides and for high purity media on request.

Pressure rating:

PN 16

Leakage rate:

Leakage rate A to P11/P12 EN 12266-1

MG	DN	Connection type code								
		0	16	17	18	37	59	60	1	31
8	4	0.58	-	-	-	-	-	-	-	-
	6	-	-	1.29	-	-	-	1.40	-	-
	8	-	-	1.52	-	-	0.70	2.57	1.4	-
	10	-	2.46	2.46	2.46	-	1.52	-	-	-
	15	-	-	-	-	-	2.34	-	-	-
10	10	-	2.81	2.81	2.81	-	2.57	3.86	-	-
	12	-	-	-	-	-	-	-	3.2	-
	15	3.86	4.45	4.45	4.45	-	2.57	4.68	3.4	-
	20	-	-	-	-	-	4.45	-	-	-
25	15	4.80	5.50	5.50	5.50	-	-	8.66	7.60	6.5
	20	7.37	8.19	8.19	8.19	-	5.15	15.44	11.70	10.0
	25	16.26	17.55	17.55	17.55	14.74	14.27	18.95	16.38	14.0
40	32	29.60	31.59	31.59	31.59	30.65	-	35.10	30.42	26.0
	40	34.28	36.15	36.15	36.15	35.33	34.52	38.38	38.61	33.0

MG = diaphragm size, Kv values in m³/h

Kv values determined in accordance with DIN EN 60534 standard, inlet pressure 5 bar, Δp 1 bar, stainless steel valve body and soft elastomer diaphragm. The Kv values for other product configurations (e.g. other diaphragm or body materials) may differ. In general, all diaphragms are subject to the influences of pressure, temperature, the process and their tightening torques. Therefore the Kv values may exceed the tolerance limits of the standard.

The Kv value curve (Kv value dependent on valve stroke) can vary depending on the diaphragm material and duration of use.

Leakage rate:	MG	DN	GGG 40.3 connection type 1, 31	GGG 40.3 connection type 8, 39	PFA / PP	Hard rubber
25		15	8.0	10.0	5.0	6.0
		20	11.5	14.0	9.0	11.0
		25	11.5	17.0	13.0	15.0
40		32	28.0	36.0	23.0	29.0
		40	28.0	40.0	26.0	32.0

MG = diaphragm size, Kv values in m³/h

Kv values determined in accordance with DIN EN 60534, inlet pressure 5 bar, Δp 1 bar, with connection flange EN 1092 length EN 558 series 1 (or threaded socket DIN ISO 228 for body material GGG40.3) and soft elastomer diaphragm. The Kv values for other product configurations (e.g. other diaphragm or body materials) may differ. In general, all diaphragms are subject to the influences of pressure, temperature, the process and their tightening torques. Therefore the Kv values may exceed the tolerance limits of the standard.

The Kv value curve (Kv value dependent on valve stroke) can vary depending on the diaphragm material and duration of use.

Product compliance

Machinery Directive: 2006/42/EC

Pressure Equipment Directive: 2014/68/EU

Food: Regulation (EC) No. 1935/2006
Regulation (EC) No. 10/2011*
FDA*
USP* Class VI

EMC Directive: 2014/30/EU

Drinking water: Belgaqua*
* depending on version and/or operating parameters

RoHS Directive: 2011/65/EU

Mechanical data

Protection class: IP 65 acc. to EN 60529

Actuating speed: Actuator size 0 Max. 3 mm/s
Actuator size 1 max. 2.5 mm/s

Weight: **Actuator**
Actuator size 0 (code 0A / 0B) 0.95 kg
Actuator size 1 (code 1A) 1.88 kg

Body

Connection type code		0, 16, 17, 18, 35, 36, 37, 55, 59, 60, 63, 64, 65	1	1	1, 31	31	6, 6K	8, 38, 39	80, 82, 88, 8A, 8E, 8P, 8T
Valve body		Spigot	Threaded socket				Threaded spigot	Flange	Clamp
Material code			12	37	90	37			
MG	DN								
8	4	0.2	-	-	-	-	-	-	-
	6	0.2	-	-	-	-	-	-	-
	8	0.2	-	-	-	-	-	-	0.33
	10	0.2	-	-	-	-	0.46	-	0.4
	15	0.2	-	-	-	-	-	-	0.4
10	10	0.66	-	-	-	-	0.73	-	0.66
	12	-	0.37	0.37	-	-	-	-	-
	15	0.66	0.57	0.57	-	-	0.77	-	0.95
	20	-	-	-	-	-	-	-	0.95
25	15	1.37	-	0.71	0.50	0.71	1.57	4.08	1.65
	20	1.28	-	0.75	0.60	0.75	1.72	5.18	1.57
	25	1.21	-	0.86	0.90	0.86	1.74	6.28	1.39
40	32	3.2	-	1.94	1.40	1.94	3.66	10.8	3.57
	40	2.91	-	2.05	1.90	2.05	3.57	12.46	3.31

MG = diaphragm size, weight in kg
Weight in lb

Mechanical environmental conditions: Class 4M8 acc. to EN 60721-3-4:1998

Vibration: 5g acc. to IEC 60068-2-6 Test Fc


Shock: 25g acc. to 60068-2-27 Test Ea

Installation position: Optional
Observe the angle of rotation for optimized draining when it comes to installation. See separate document, "Angle of rotation technical information".


Actuator duty cycle and service life

Service life: **Control operation** - Class C according to EN 15714-2 (1,800,000 starts and 1200 starts per hour).
Open/Close duty - At least 500,000 switching cycles at room temperature and permissible duty cycle.

Duty cycle: Control module Open/Close control (code AE, A5, A6)
 Duty cycle with full valve lift and playing time 10 minutes.



Control module Positioner (code S0, S5, S6), Open/Close duty



Control module positioner (code S0, S5, S6), control operation - class C acc. to EN 15714-2

- DN 4 - 25 (code 0A) up to 60 °C ambient temperature
- DN 32 - 40 (code 1A) up to 30 °C ambient temperature

The specified characteristics and values apply to the default setting.

With reduced forces, higher duty cycles and/or higher ambient temperatures are possible. At higher force settings the duty cycle and/or ambient temperature is reduced (for IO-Link parameters see operating instructions).

Electrical data

Supply voltage Uv:	24 V DC \pm 10%	
Rating:	Actuator size 0 (code 0A, 0B)	20 W
	Actuator size 1 (code 1A)	60 W
Operation:	Stepper motor, self-locking	
Reverse battery protection:	Yes	

Analogue input signals – Control module Positioner (code S0, S5, S6)

Set value

Input signal:	0/4 - 20 mA; 0 - 10 V (function selectable via IO-Link)	
Input type:	passive	
Input resistance:	250 Ω	
Accuracy/linearity:	$\leq \pm 0.3\%$ of full flow	
Temperature drift:	$\leq \pm 0.1\%$ / 10°K	
Resolution:	12 bit	
Reverse battery protection:	Yes (up to \pm 24 V DC)	

Digital input signals

Inputs:	Function selectable via IO-Link (see table Overview of available functions – Input and output signals)	
Input voltage:	24 V DC	
Logic level "1":	> 15.3 V DC	
Logic level "0":	< 5.8 V DC	
Input current:	typically < 0.5 mA	

Analogue output signals – Control module Positioner (code S0, S5, S6)

Actual value

Output signal:	0/4 - 20 mA; 0 - 10 V (function selectable via IO-Link)	
Output type:	Active	
Accuracy:	$\leq \pm 1\%$ of full flow	
Temperature drift:	$\leq \pm 0.1\%$ / 10°K	
Load resistor:	≤ 750 k Ω	
Resolution:	12 bit	
Short-circuit proof:	Yes	

Digital output signals

Outputs:	Function selectable via IO-Link (see table Overview of available functions – Input and output signals)
Type of contact:	Push-Pull
Switching voltage:	Power supply U_v
Switching current:	≤ 140 mA
Short-circuit proof:	Yes


Communication

Interface:	IO-Link
Function:	Parameterization/process data
Transmission rate:	38400 baud
Frame type in Operate:	2.5 (eSyStep ON/OFF, code AE, A5, A6) 2.V (eSyStep positioner, code S0, S5, S6), PDout 3Byte; PDin 3 Byte; OnRequestData 2 Byte
Min. cycle time:	2.3 ms (eSyStep ON/OFF, code AE, A5, A6) 20 ms (eSyStep positioner, code S0, S5, S6)
Vendor-ID:	401
Device-ID:	1906701 (eSyStep ON/OFF, code AE, A5, A6) 1906801 (eSyStep positioner, code S0, S5, S6),
Product-ID:	eSyStep On/Off (code AE, A5, A6) eSyStep Positioner (code S0, S5, S6)
ISDU support:	Yes
SIO operation:	Yes
IO-Link specification:	V1.1

IODD files can be downloaded via <https://ioddfinder.io-link.com/> or www.gemu-group.com.


Electrical connection

Position of the connectors



Electrical connection


Connection X1



7-pin plug, Binder, type 693

Pin	Signal name
1	Uv, 24 V DC supply voltage
2	GND
3	Digital input 1
4	Digital input 2
5	Digital input/output
6	Digital output, IO-Link
7	n.c.

Connection X2 (only for positioner design)




5-pin M12 plug, A-coded

Pin	Signal name
1	I+/U+, set value input
2	I-/U-, set value input
3	I+/U+, actual value output
4	I-/U-, actual value output
5	n.c.

Dimensions

Actuator dimensions



MG	DN	Actuator version	A	A1	A2	B	B1	B2
8	4 - 15	0B	8.76	2.28	1.31	2.34	3.19	5.26
10	10 - 20	0A	9.33	2.85	1.31	2.34	3.19	5.26
25	15 - 25	1A	12.05	4.88	1.28	2.76	3.23	5.91
40	32 - 40	1A	11.97	4.80	1.28	2.76	3.23	5.91

Dimensions in inch


MG = diaphragm size

Dimension A2 only for control module – positioner (code S0, S5, S6)

* CT = A + H1 (see body dimensions)

Body dimensions

Spigot DIN/EN ISO (code 0, 16, 17, 18, 60)



Connection type spigot DIN/EN/ISO (code 0, 16, 17, 18, 60)¹⁾, forged material (code 40, 42, F4)²⁾

MG	DN	NPS	c (min)	ød					H1	L	s				
				Connection type							Connection type				
				0	16	17	18	60			0	16	17	18	60
8	4	-	0.79	0.24	-	-	-	-	0.33	2.83	0.04	-	-	-	-
	6	-	0.79	-	-	0.31	-	0.40	0.33	2.83	-	-	0.04	-	0.06
	8	1/4"	0.79	-	-	0.39	-	0.53	0.33	2.83	-	-	0.04	-	0.06
	10	3/8"	0.79	-	0.47	0.51	0.55	-	0.33	2.83	-	0.04	0.06	0.08	-
10	10	3/8"	0.98	-	0.47	0.51	0.55	0.68	0.49	4.25	-	0.04	0.06	0.08	0.06
	15	1/2"	0.98	0.71	0.71	0.75	0.79	0.84	0.49	4.25	0.06	0.04	0.06	0.08	0.06
25	15	1/2"	0.98	0.71	0.71	0.75	0.79	0.84	0.75	4.72	0.06	0.04	0.06	0.08	0.06
	20	3/4"	0.98	0.87	0.87	0.91	0.94	1.06	0.75	4.72	0.06	0.04	0.06	0.08	0.06
	25	1"	0.98	1.10	1.10	1.14	1.18	1.33	0.75	4.72	0.06	0.04	0.06	0.08	0.08
40	32	1 1/4"	0.98	1.34	1.34	1.38	1.42	1.67	1.02	6.02	0.06	0.04	0.06	0.08	0.08
	40	1 1/2"	1.20	1.57	1.57	1.61	1.65	1.90	1.02	6.02	0.06	0.04	0.06	0.08	0.08

Dimensions in inch

MG = diaphragm size

1) **Connection type**

Code 0: Spigot DIN

Code 16: Spigot DIN EN 10357 series B (2014 edition; formerly DIN 11850 series 1)

Code 17: Spigot EN 10357 series A/DIN 11866 series A formerly DIN 11850 series 2

Code 18: Spigot DIN 11850 series 3


Code 60: Spigot ISO 1127/DIN EN 10357 series C (2014 edition)/DIN 11866 series B

2) **Valve body material**

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code F4: 1.4539, forged body



Connection type spigot DIN/EN/ISO (code 0, 17, 60)¹⁾, investment casting material (code C3)²⁾

MG	DN	NPS	c (min)	ød			H1	L	s		
				Connection type					Connection type		
				0	17	60			0	17	60
8	4	-	0.79	0.24	-	-	0.33	2.83	0.04	-	-
	6	-	0.79	-	0.31	-	0.33	2.83	-	0.04	-
	8	1/4"	0.79	-	0.39	0.53	0.33	2.83	-	0.04	0.06
	10	3/8"	0.79	-	0.51	-	0.33	2.83	-	0.06	-
10	10	3/8"	0.98	-	0.51	0.68	0.49	4.25	-	0.06	0.06
	15	1/2"	0.98	-	0.75	0.84	0.49	4.25	-	0.06	0.06
25	15	1/2"	0.98	-	0.75	0.84	0.51	4.72	-	0.06	0.06
	20	3/4"	0.98	-	0.91	1.06	0.63	4.72	-	0.06	0.06
	25	1"	0.98	-	1.14	1.33	0.75	4.72	-	0.06	0.08
40	32	1 1/4"	0.98	-	1.38	1.67	0.94	6.02	-	0.06	0.08
	40	1 1/2"	1.20	-	1.61	1.90	1.02	6.02	-	0.06	0.08

Dimensions in inch

MG = diaphragm size

1) **Connection type**

Code 0: Spigot DIN


Code 17: Spigot EN 10357 series A/DIN 11866 series A formerly DIN 11850 series 2

Code 60: Spigot ISO 1127/DIN EN 10357 series C (2014 edition)/DIN 11866 series B

2) **Valve body material**

Code C3: 1.4435, investment casting

Spigot ASME/BS (code 55, 59, 63, 64, 65)



Connection type spigot ASME/BS (code 55, 59, 63, 64, 65)¹⁾, forged material (code 40, 42, F4)²⁾

MG	DN	NPS	c (min)	ød					H1	L	s				
				Connection type							Connection type				
				55	59	63	64	65			55	59	63	64	65
8	6	-	0.79	-	-	0.41	-	0.41	0.33	2.83	-	-	0.05	-	0.07
	8	1/4"	0.79	0.25	0.25	0.54	-	0.54	0.33	2.83	0.05	0.04	0.06	-	0.09
	10	3/8"	0.79	0.38	0.38	-	-	-	0.33	2.83	0.05	0.04	-	-	-
	15	1/2"	0.79	0.50	0.50	-	-	-	0.33	2.83	0.05	0.06	-	-	-
10	10	3/8"	0.98	0.38	0.38	0.67	-	0.67	0.49	4.25	0.05	0.04	0.06	-	0.09
	15	1/2"	0.98	0.50	0.50	0.84	0.84	0.84	0.49	4.25	0.05	0.06	0.08	0.06	0.11
	20	3/4"	0.98	0.75	0.75	-	-	-	0.49	4.25	0.05	0.06	-	-	-
25	15	1/2"	0.98	-	-	0.84	0.84	0.84	0.75	4.72	-	-	0.08	0.06	0.11
	20	3/4"	0.98	0.75	0.75	1.05	1.05	1.05	0.75	4.72	0.05	0.06	0.08	0.06	0.11
	25	1"	0.98	-	1.00	1.31	1.31	1.31	0.75	4.72	-	0.06	0.11	0.06	0.13
40	32	1 1/4"	0.98	-	-	1.66	1.66	1.66	1.02	6.02	-	-	0.11	0.06	0.14
	40	1 1/2"	1.20	-	1.50	1.90	1.90	1.90	1.02	6.02	-	0.06	0.11	0.06	0.14

Connection type spigot ASME BPE (code 59)¹⁾, investment casting material (code C3)²⁾

MG	DN	NPS	c (min)	ød	H1	L	s
8	8	1/4"	0.79	0.25	0.33	2.83	0.04
	10	3/8"	0.79	0.38	0.33	2.83	0.04
	15	1/2"	0.79	0.50	0.33	2.83	0.06
10	20	3/4"	0.98	0.75	0.49	4.25	0.06
25	20	3/4"	0.98	0.75	0.63	4.72	0.06
	25	1"	0.98	1.00	0.75	4.72	0.06
40	32	1 1/4"	0.98	-	-	6.02	-
	40	1 1/2"	1.20	1.50	1.02	6.02	0.06

Dimensions in inch

MG = diaphragm size

1) **Connection type**

Code 55: Spigot BS 4825, part 1

Code 59: Spigot ASME BPE / DIN 11866 series C

Code 63: Spigot ANSI/ASME B36.19M Schedule 10s

Code 64: Spigot ANSI/ASME B36.19M schedule 5s

Code 65: Spigot ANSI/ASME B36.19M Schedule 40s


2) **Valve body material**

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code C3: 1.4435, investment casting

Code F4: 1.4539, forged body

Spigot JIS/SMS (code 35, 36, 37)**Connection type spigot JIS/SMS (code 35, 36, 37)¹⁾, forged material (code 40, 42, F4)²⁾**

MG	DN	NPS	c (min)	ød			H1	L	s		
				Connection type					Connection type		
				35	36	37			35	36	37
8	6	-	0.79	-	0.41	-	0.33	2.83	-	0.05	-
	8	1/4"	0.79	-	0.54	-	0.33	2.83	-	0.06	-
10	10	3/8"	0.98	-	0.68	-	0.49	4.25	-	0.06	-
	15	1/2"	0.98	-	0.85	-	0.49	4.25	-	0.08	-
25	15	1/2"	0.98	-	0.85	-	0.75	4.72	-	0.08	-
	20	3/4"	0.98	-	1.07	-	0.75	4.72	-	0.08	-
	25	1"	0.98	1.00	1.34	0.98	0.75	4.72	0.05	0.11	0.05
40	32	1 1/4"	0.98	1.25	1.68	1.33	1.02	6.02	0.05	0.11	0.05
	40	1 1/2"	1.20	1.50	1.91	1.50	1.02	6.02	0.05	0.11	0.05

Connection type spigot SMS (code 37)¹⁾, investment casting material (code C3)²⁾

MG	DN	NPS	c (min)	ød	H1	L	s
25	25	1"	0.98	0.98	0.75	4.72	0.05
40	40	1 1/2"	1.20	1.50	1.02	6.02	0.05

Dimensions in inch

MG = diaphragm size

1) Connection type

Code 35: Spigot JIS-G 3447

Code 36: Spigot JIS-G 3459 schedule 10s

Code 37: Spigot SMS 3008

2) Valve body material


Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code C3: 1.4435, investment casting

Code F4: 1.4539, forged body

Threaded socket DIN (code 1)



Connection type threaded socket (code 1)¹⁾, brass material (code 12)²⁾

MG	DN	NPS	H	H1	L	n	R	SW 2	t
10	12	3/8"	9.06	4.33	21.65	2	G 3/8	8.66	5.12
	15	1/2"	11.42	5.51	29.53	2	G 1/2	9.84	5.91

Connection type threaded socket (code 1)¹⁾, investment casting material (code 37)²⁾

MG	DN	NPS	H	H1	L	n	R	SW 2	t
8	8	1/4"	7.48	3.54	28.35	6	G 1/4	7.09	4.33
10	12	3/8"	9.84	5.12	21.65	2	G 3/8	8.66	4.72
	15	1/2"	11.81	5.91	26.77	2	G 1/2	10.63	5.91
25	15	1/2"	11.42	6.3	33.46	6	G 1/2	10.63	5.91
	20	3/4"	12.6	6.3	33.46	6	G 3/4	12.6	6.3
	25	1"	14.57	6.3	43.31	6	G 1	16.14	5.12
40	32	1 1/4"	19.29	9.45	47.24	8	G 1 1/4	19.69	7.87
	40	1 1/2"	20.47	9.45	55.12	8	G 1 1/2	21.65	7.09

Connection type threaded socket (code 1)¹⁾, SG iron material (code 90)²⁾

MG	DN	NPS	H	H1	L	n	R	SW 2	t
25	15	1/2"	1.29	0.66	3.35	6	G 1/2	32	0.59
	20	3/4"	1.65	0.85	3.35	6	G 3/4	41	0.64
	25	1"	1.84	0.93	4.33	6	G 1	46	0.75
40	32	1 1/4"	2.20	1.12	4.72	6	G 1 1/4	55	0.84
	40	1 1/2"	2.60	1.32	5.51	6	G 1 1/2	65	0.84

Dimensions in inch

MG = diaphragm size

n = number of flats

1) **Connection type**


Code 1: Threaded socket DIN ISO 228

2) **Valve body material**

Code 12: CW614N, CW617N (brass)

Code 37: 1.4408, investment casting

Code 90: EN-GJS-400-18-LT (GGG 40.3)

Threaded socket NPT (code 31)**Connection type threaded socket NPT (code 31)¹⁾, investment casting material (code 37)²⁾**

MG	DN	NPS	H	H1	L	n	R	SW 2	t
25	15	1/2"	11.42	6.3	33.46	6	NPT 1/2	10.63	5.51
	20	3/4"	12.6	6.3	33.46	6	NPT 3/4	12.6	5.51
	25	1"	16.54	8.27	43.31	6	NPT 1	16.14	6.69
40	32	1 1/4"	19.29	9.45	47.24	8	NPT 1 1/4	19.69	6.69
	40	1 1/2"	20.47	9.45	55.12	8	NPT 1 1/2	21.65	6.69

Connection type threaded socket NPT (code 31)¹⁾, SG iron material (code 90)²⁾

MG	DN	NPS	H	H1	L	n	R	SW 2	t
25	15	1/2"	1.29	0.66	3.35	6	NPT 1/2	32	0.54
	20	3/4"	1.65	0.85	3.35	6	NPT 3/4	41	0.56
	25	1"	1.84	0.93	4.33	6	NPT 1	46	0.66
40	32	1 1/4"	2.20	1.12	4.72	6	NPT 1 1/4	55	0.68
	40	1 1/2"	2.60	1.32	5.51	6	NPT 1 1/2	65	0.68

Dimensions in inch

MG = diaphragm size

n = number of flats

1) Connection type


Code 31: NPT female thread

2) Valve body material

Code 37: 1.4408, investment casting

Code 90: EN-GJS-400-18-LT (GGG 40.3)

Threaded spigot DIN (code 6)



Connection type threaded spigot DIN (code 6)¹⁾, forged material (code 40, 42)²⁾

MG	DN	NPS	ød1	H1	L	R
8	10	3/8"	3.94	3.35	36.22	Rd 28 x 1/8
10	10	3/8"	3.94	4.92	46.46	Rd 28 x 1/8
	15	1/2"	6.3	4.92	46.46	Rd 34 x 1/8
25	15	1/2"	6.3	7.48	46.46	Rd 34 x 1/8
	20	3/4"	7.87	7.48	46.46	Rd 44 x 1/6
	25	1"	10.24	7.48	50.39	Rd 52 x 1/6
40	32	1¼"	12.6	10.24	57.87	Rd 58 x 1/6
	40	1½"	14.96	10.24	62.99	Rd 65 x 1/6

Dimensions in inch

MG = diaphragm size

1) Connection type


Code 6: Threaded spigot DIN 11851

2) Valve body material

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Cone spigot DIN (code 6K)



Connection type cone spigot DIN (code 6K)¹⁾, forged material (code 40, 42)²⁾

MG	DN	NPS	ød1	H1	L	R
8	10	3/8"	10.0	8.5	90.0	Rd 28 x 1/8
10	10	3/8"	10.0	12.5	116.0	Rd 28 x 1/8
	15	1/2"	16.0	12.5	116.0	Rd 34 x 1/8
25	15	1/2"	16.0	19.0	116.0	Rd 34 x 1/8
	20	3/4"	20.0	19.0	114.0	Rd 44 x 1/6
	25	1"	26.0	19.0	127.0	Rd 52 x 1/6
40	32	1 1/4"	32.0	26.0	147.0	Rd 58 x 1/6
	40	1 1/2"	38.0	26.0	160.0	Rd 65 x 1/6

Dimensions in inch

MG = diaphragm size

1) Connection type


Code 6K: Cone spigot and union nut DIN 11851

2) Valve body material

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Flange EN (code 8)



Connection type flange, length EN 558 (code 8)¹⁾, SG iron material (code 17, 18, 83, 90), investment casting material (code 39, C3), forged material (code 40, 42)²⁾

MG	DN	NPS	øD	FTF		H1				øk	øL	n
				Material		Material						
				17, 18, 39, 83, 90	40, 42, C3	17, 18, 39, 83	40, 42	C3	90			
25	15	1/2"	3.74	5.12	59.06	7.09	7.48	5.12	0.55	2.56	5.51	4
	20	3/4"	4.18	5.91	59.06	8.07	7.48	6.3	0.65	2.95	5.51	4
	25	1"	4.53	6.30	62.99	9.06	7.48	7.48	0.77	3.35	5.51	4
40	32	1 1/4"	5.51	7.09	70.87	11.3	10.24	9.45	0.91	3.94	7.48	4
	40	1 1/2"	5.91	7.87	78.74	12.99	10.24	10.24	1.06	4.33	7.48	4

Dimensions in inch

MG = diaphragm size

n = number of bolts

1) **Connection type**

Code 8: Flange EN 1092, PN 16, form B, face-to-face dimension FTF EN 558 series 1, ISO 5752, basic series 1, length only for body configuration D

2) **Valve body material**

Code 17: EN-GJS-400-18-LT (GGG 40.3), PFA lined

Code 18: EN-GJS-400-18-LT (GGG 40.3), PP lined

Code 39: 1.4408, PFA lined


Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code 83: EN-GJS-400-18-LT (GGG 40.3), hard rubber lined

Code 90: EN-GJS-400-18-LT (GGG 40.3)

Code C3: 1.4435, investment casting

Flange JIS (code 34)**Connection type flange, length 558 (code 34)¹⁾, investment casting material (code 39)²⁾**

MG	DN	NPS	øD	FTF	H1	øk	øL	n
25	15	1/2"	3.74	5.12	0.71	2.76	0.59	4
	20	3/4"	3.94	5.91	0.81	2.95	0.59	4
	25	1"	4.92	6.30	0.91	3.54	0.75	4
40	32	1¼"	5.31	7.09	1.13	3.94	0.75	4
	40	1½"	5.51	7.87	1.30	4.13	0.75	4

Dimensions in inch

MG = diaphragm size


1) Connection type

Code 34: Flange JIS B2220, 10K, RF, face-to-face dimension FTF EN 558 series 1, ISO 5752, basic series 1, length only for body configuration D

2) Valve body material

Code 39: 1.4408, PFA lined

Flange ANSI Class (code 38, 39)



Connection type flange, length MSS SP-88 (code 38)¹⁾, SG iron material (code 17, 18, 83), investment casting material (code 39)²⁾

MG	DN	NPS	øD	FTF		H1	øk	øL	n
				Material					
				17, 18, 39	83				
25	20	3/4"	3.94	5.75	5.76	8.07	2.75	6.26	4
	25	1"	4.33	5.75	5.76	9.06	3.13	6.26	4
40	40	1½"	4.92	6.89	6.75	12.99	3.87	6.26	4

Connection type flange, length EN 558 (code 39)¹⁾, SG iron material (code 17, 18, 83, 90), investment casting material (code 39, C3), forged material (code 40, 42)²⁾

MG	DN	NPS	øD	FTF		H1				øk	øL	n
				Material		Material						
				17, 18, 39, 83, 90	40, 42, C3	17, 18, 39, 83	C3	40, 42	90			
25	15	1/2"	3.54	150.0	5.91	7.09	5.12	7.48	0.55	2.37	6.26	4
	20	3/4"	3.94	150.0	5.91	8.07	6.3	7.48	0.65	2.75	6.26	4
	25	1"	4.33	160.0	6.30	9.06	7.48	7.48	0.77	3.13	6.26	4
40	32	1¼"	4.53	180.0	7.09	11.3	9.45	10.24	0.91	3.50	6.26	4
	40	1½"	4.92	200.0	7.87	12.99	10.24	10.24	1.06	3.87	6.26	4

Dimensions in inch

MG = diaphragm size

n = number of bolts

1) **Connection type**

Code 38: Flange ANSI Class 150 RF, length only for body configuration D acc. to MSS SP-88

Code 39: Flange ANSI Class 125/150 RF, length only for body configuration D acc. to EN 558 series 1, ISO 5752, basic series 1

2) **Valve body material**

Code 17: EN-GJS-400-18-LT (GGG 40.3), PFA lined

Code 18: EN-GJS-400-18-LT (GGG 40.3), PP lined

Code 39: 1.4408, PFA lined


Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code 83: EN-GJS-400-18-LT (GGG 40.3), hard rubber lined

Code 90: EN-GJS-400-18-LT (GGG 40.3)

Code C3: 1.4435, investment casting

Clamp (code 80, 82, 88, 8A, 8E, 8P, 8T)**Connection type clamp DIN/ASME (code 80, 88, 8P, 8T)¹⁾, forged material (code 40, 42, F4)²⁾**

MG	DN	NPS	ød1		ød3		H1	L	
			Connection type		Connection type			Connection type	
			80, 8P	88, 8T	80, 8P	88, 8T		80, 8P	88, 8T
8	8	1/4"	17.99	-	9.84	-	3.35	25	-
	10	3/8"	30.51	-	9.84	-	3.35	25	-
	15	1/2"	37.01	37.01	9.84	9.84	3.35	25	42.52
10	15	1/2"	37.01	37.01	9.84	9.84	4.92	35	42.52
	20	3/4"	62.01	62.01	9.84	9.84	4.92	40	46.06
25	20	3/4"	62.01	62.01	9.84	9.84	7.48	40	46.06
	25	1"	87.01	87.01	19.88	19.88	7.48	45	50
40	40	1½"	137.01	137.01	19.88	19.88	10.24	55	62.6

Dimensions in inch

MG = diaphragm size

1) Connection type

Code 80: Clamp ASME BPE, length only for body configuration D acc. to ASME BPE

Code 82: Clamp DIN 32676 series B, face-to-face dimension FTF EN 558 series 7, length only for body configuration D

Code 88: Clamp ASME BPE, for pipe ASME BPE, face-to-face dimension FTF EN 558 series 7, length only for body configuration D

Code 8A: Clamp DIN 32676 series A, face-to-face dimension FTF acc. to EN 558 series 7, length only for body configuration D

Code 8E: Clamp ISO 2852 for pipe ISO 2037, clamp SMS 3017 for pipe SMS 3008 face-to-face dimension FTF EN 558 series 7, length only for body configuration D


2) Valve body material

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code F4: 1.4539, forged body

Dimensions



Connection type clamp DIN/ISO (code 82, 8A, 8E)¹⁾, forged material (code 40, 42, F4)²⁾

MG	DN	NPS	ød1			ød3			H1	L		
			Connection type			Connection type				Connection type		
			82	8A	8E	82	8A	8E		82	8A	8E
8	6	1/8"	2.76	2.36	-	9.84	9.84	-	3.35	25	25	-
	8	1/4"	4.06	3.15	-	9.84	9.84	-	3.35	25	25	-
	10	3/8"	-	3.94	-	-	13.39	-	3.35	-	35	-
10	10	3/8"	5.51	3.94	-	9.84	13.39	-	4.92	42.52	42.52	-
	15	1/2"	7.13	6.3	-	19.88	13.39	-	4.92	42.52	42.52	-
25	15	1/2"	7.13	6.3	-	19.88	13.39	-	7.48	42.52	42.52	-
	20	3/4"	9.33	7.87	-	19.88	13.39	-	7.48	46.06	46.06	-
	25	1"	11.69	10.24	8.9	19.88	19.88	19.88	7.48	50	50	50
40	32	1 1/4"	15.12	12.6	12.32	25.2	19.88	19.88	10.24	57.48	57.48	57.48
	40	1 1/2"	17.44	14.96	14.02	25.2	19.88	19.88	10.24	62.6	62.6	62.6

Dimensions in inch

MG = diaphragm size

1) Connection type

Code 80: Clamp ASME BPE, length only for body configuration D acc. to ASME BPE

Code 82: Clamp DIN 32676 series B, face-to-face dimension FTF EN 558 series 7, length only for body configuration D

Code 88: Clamp ASME BPE, for pipe ASME BPE, face-to-face dimension FTF EN 558 series 7, length only for body configuration D

Code 8A: Clamp DIN 32676 series A, face-to-face dimension FTF acc. to EN 558 series 7, length only for body configuration D

Code 8E: Clamp ISO 2852 for pipe ISO 2037, clamp SMS 3017 for pipe SMS 3008 face-to-face dimension FTF EN 558 series 7, length only for body configuration D

2) Valve body material

Code 40: 1.4435 (F316L), forged body

Code 42: 1.4435 (BN2), forged body, Fe < 0.5%

Code F4: 1.4539, forged body

Accessories



**GEMÜ 1218
Connector**

The GEMÜ 1218 is a connector (cable socket / cable plug), 7-pin. Straight and/or 90° angled plug type.

GEMÜ 1218 Binder connector			
Connection X1 – supply voltage, relay outputs			
Binder plug	468/eSy series mating connector	Terminal compartment/ screws, 7-pin	88220649 ¹⁾
		Terminal compartment/ screws, 7-pin, 90°	88377714
		Terminal compartment/ screws, 7-pin, 90°, fitted with a 2 metre cable set	88770522

1) provided in the scope of delivery



**GEMÜ 1219
Cable socket / cable plug M12**

The GEMÜ 1219 is a connector (cable socket / cable plug) M12, 5-pin. Straight and/or 90° angled plug type. Defined cable length or with threaded connection without cable. Various materials available for the threaded ring.

Suitable for electrical connection of the connector X2

Description	Length	Order number
5-pin, angle	without cable	88205545 ¹⁾
	2 m cable	88205534
	5 m cable	88205540
	10 m cable	88210911
	15 m cable	88244667
5-pin, straight	without cable	88205544
	2 m cable	88205542
	5 m cable	88205543
	10 m cable	88270972
	15 m cable	88346791

1) provided in the scope of delivery for control module code S0



GEMÜ 1560
IO-Link master

The GEMÜ 1560 IO-Link master is used for parametrization, actuation, commissioning and for evaluating process and diagnostics data on products with IO-Link interface with communication standard in accordance with IEC 61131-9. The IO-Link master is available with USB port for use on a computer or with a Bluetooth or WLAN interface for use on mobile devices (iOS and Android). GEMÜ 1560 can be ordered separately or as a set for GEMÜ products including the required adapter.

Description	Order designation	Order number
IO-Link master kit (adapter plus cable)	1560USBS 1 A40A12AU A	99072365
IO-Link master kit (adapter plus cable)	1560 BTS 1 A20A12AA A	99130458



GEMÜ 1571
Emergency power supply module

The GEMÜ 1571 capacitive emergency power supply module is suitable for valves with motorized actuators such as GEMÜ eSyStep and eSyDrive as well as the GEMÜ C53 iComLine control valve. In the event of a power failure, the product provides an uninterrupted power supply so that the valve can be moved to the safety position. The emergency power supply module is available individually or with an expansion module and can supply several valves. The input and output voltage is 24 V.

GEMÜ 1571 emergency power supply module			
Input voltage	Output voltage	Capacity	Item number
24 V	24 V	1700 Ws	88660398
24 V	24 V	13200 Ws	88751062



GEMÜ 1573
Switching power supply unit

The GEMÜ 1573 switching power supply unit converts unstable input voltages from 100 to 240 V AC into a continuous DC voltage. It can be used as an accessory for valves with motorized actuators e. g. GEMÜ eSyLite, eSyStep und eSyDrive and for additional devices with a 24 V DC power supply. Different power levels, output currents and a 48 V DC version for servoDrive actuators are available.

GEMÜ 1573 switching power supply unit			
Input voltage	Output voltage	Output current	Item number
100 - 240 V AC	24 V DC	5 A	88660400
		10 A	88660401



GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG
Fritz-Müller-Straße 6-8, 74653 Ingelfingen-Criesbach, Germany
Tel. +49 (0)7940 123-0 · info@gemue.de
www.gemu-group.com